


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Switching Power Supply
Name and address of the applicant	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Name and address of the manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Name and address of the factory	ALPS LOGISTICS FACILITIES CO LTD 593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831 JAPAN
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	See Page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 62368-1:2014/ A11:2017. National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E122103-A6059-CB-1 issued on 2019-03-26, E122103-A6059-CB-1 issued on 2019-03-25

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pflugsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-03-27

Signature:



Masamichi Takagi

Model Details:

HWS30A-3, HWS30A-5, HWS30A-12, HWS30A-15, HWS30A-24, HWS30A-48.

Maybe followed by optional suffix "abcde" (a is "/", b is "HD", c is "A", d is "FG", e is "DIN"; "a", "b", "c", "d", "e" may be blank)

HWS30A-3/B200V, HWS30A-5/B200V, HWS30A-12/B200V, HWS30A-15/B200V, HWS30A-24/B200V, HWS30A-48/B200V.

Maybe followed by optional suffix "bde" (b is "HD", d is "FG", e is "DIN"; "b", "d", "e" may be blank)

Factories:

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD

TONGXIN RD ZHAOFENG ECONOMIC DEVELOPMENT ZONE LEYU TOWN ZHANGJIAGANG JIANGSU 215622
CHINA

TDK-LAMBDA CORP

2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

SENDAN ELECTRONICS MFG CO LTD

1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756
JAPAN

TDK-LAMBDA MALAYSIA SDN BHD

LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN
MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD

PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI
MALAYSIA

WUXI TDK-LAMBDA ELECTRONICS CO LTD

NO 6 XING CHUANG ER LU WUXI JIANGSU 214028
CHINA

Ratings:

Input:

AC100-240 V, 50-60 Hz, 0.5 A (for model HWS30A-3) and 0.7 A (for all models except for HWS30A-3)

AC200-240V, 50-60 Hz, 0.35 A (for model HWS30A-3/B200V) and 0.45 A (for models HWS30A-5/B200V,
HWS30A-12/B200V, HWS30A-15/B200V, HWS30A-24/B200V, and HWS30A-48/B200V)

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-03-27

Signature:

Masamichi Takagi