

Certificate



Certificate no.

TA 50373180 01

License Holder:

TDK-Lambda Americas Inc.
401 Mile of Cars Way, Suite 325,
National City, CA 91950
USA

Manufacturing Plant:

ZTW1-LinPr-10049856 001

Test report no.: ZTW1-SCL 10049856 001

Client Reference: RD06-13022017-Co.TDK

Tested to: IEC 60601-1:2005+A1
EN 60601-1:2006+A11+A1+A12

Certified Product: (Switching Power Supply)

License Fee - Units

Type Designation	: CSS65A-XZZZZZ (TDK-Lambda)	5
X stands for	: 5, 12, 15, 19, 24, 28, 48, 54	1
Z stands for	: a-z, A-Z, 0-9	1
Rated Voltage	: AC 100-240V, 50-60Hz	
Rated Current	: 2-1A	
Output Voltage	: see Appendix	
Output Current	: see Appendix	
max. Ambient Temperature:	50°C	
Protection Class	: I	

Remark: 1. This risk management requirements of the standard were not addressed.
2. This certificate is valid for maximum 5 years.

7

Licensed Test mark:



TÜV Rheinland Taiwan Ltd

Signature

Dipl.-Ing. W. Hsu



Date of Issue
(day/mo/yr)

07/03/2017

Appendix to TÜV approved Certificate No.: TA 50373180

Certified Product : Switching Power Supply
 Report Number : 10049856 001
 Type Designation : CSS65A-XZZZZZ
 (X = 5, 12, 15, 19, 24, 28, 48, 54; Z = a-z, A-Z, 0-9)

Model name	Output rating		
	V	A	W
CSS65A-5ZZZZZ	+5	8	40
CSS65A-12ZZZZZ	+12	5.42	65
CSS65A-15ZZZZZ	+15	4.34	65
CSS65A-19ZZZZZ	+19	3.43	65
CSS65A-24ZZZZZ	+24	2.71	65
CSS65A-28ZZZZZ	+28	2.33	65
CSS65A-48ZZZZZ	+48	1.36	65
CSS65A-54ZZZZZ	+54	1.21	65

Date: 7th March, 2017

Certification Body


 Dipl.-Ing. W. Hsu

