

Certificate



Certificate no.

TA 50364837 01

License Holder:

TDK-Lambda Americas Inc.
401 Mile of Cars Way, Suite 325,
National City, CA 91950
USA

Manufacturing Plant:

ZTW1-LinPr-10052285 001

Test report no.: ZTW1-SCL 10052285 001

Client Reference: 2Co-license

Tested to:

IEC 60601-1:2005+A1
EN 60601-1:2006+A11+A1+A12

Certified Product: AC Power Adapter

License Fee - Units

Type Designation	: DTM300PWXXD2-ZZZZZ (TDK-Lambda)	5
XXX stands for	: 120, 190, 240, 280, 480 or 540	1
Z stands for	: 0-9, A-Z or blank	1
Rated Voltage	: AC 100-240V, 50-60Hz	
Rated Current	: 3.3-1.4A	
Outputs	: see Appendix	
max. Power Output	: see Appendix	
max. Ambient Temperature:	+40°C	
Protection Class	: II	

Remarks: 1. The risk management requirements of the standard were not addressed;
2. This certificate is valid for maximum 5 years.

7

Licensed Test mark:



TÜV Rheinland Taiwan Ltd

Signature

Date of Issue
(day/mo/yr)

22/11/2016



Dipl.-Ing. (FH) A. Klinker

Appendix to TÜV approved Certificate No.: TA 50364837

Certified Product : AC Power Adapter
Report Number : 10052285 001
Type Designation : DTM300PWXXD2-ZZZZZ
(XXX can be 120, 190, 240, 280, 480, or 540, Z can be 0- 9, A-Z or blank)

Model	Output voltage	Output current	Maximum Watt
DTM300PW120D2-ZZZZZ	+12V	25A	300W
DTM301PW190D2-ZZZZZ	+19V	15.79A	300W
DTM302PW240D2-ZZZZZ	+24V	12.5A	300W
DTM303PW280D2-ZZZZZ	+28V	10.71A	300W
DTM304PW480D2-ZZZZZ	+48V	6.25A	300W
DTM305PW540D2-ZZZZZ	+54V	5.56A	300W

Date: 22nd Nov., 2016



Certification Body



Dipl.-Ing. (FH) A. Klinker