



Ref. Certif. No.

**DK-88676-UL**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product

Medical Switch Mode Power Supply

Name and address of the applicant

TDK-LAMBDA UK LTD  
KINGSLEY AVE, ILFRACOMBE DEVON EX34 8ES  
UNITED KINGDOM

Name and address of the manufacturer

TDK-LAMBDA UK LTD  
KINGSLEY AVE, ILFRACOMBE DEVON EX34 8ES  
UNITED KINGDOM

Name and address of the factory

Note: When more than one factory, please report on page 2

TDK-LAMBDA UK LTD  
KINGSLEY AVE, ILFRACOMBE DEVON EX34 8ES  
UNITED KINGDOM

[Additional Information on page 2](#)

Ratings and principal characteristics

94.5-240Vac nom, 45-63Hz, 6.1A rms max. or 100-240Vac nom, 45-63Hz, 6.1A rms max. (See Model Differences for details of ratings)



Trademark / Brand (if any)

Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

EFE400M or EFE-400M series  
See Page 2

Additional information (if necessary may also be reported on page 2)

The risk management requirements of the standard were not addressed. National Differences specified in the CB Test Report.

[Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005

As shown in the Test Report Ref. No. which forms part of this Certificate

E349607-D1012-1/A0/C0-CB issued on 2019-10-06

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-10-18

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

**DK-88676-UL**

Model Details:  
EFE400M or EFE-400M series  
(see Model Differences for details of models and nomenclature)

Factories:  
PANYU TRIO MICROTRONIC CO., LTD,  
SHIJI INDUSTRIAL ESTATE, DONGYONG, NANSHA GUANGZHOU, GUANGDONG  
CHINA

**Additional information (if necessary)**



- UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-10-18

Signature:

Jan-Erik Storgaard