



Power Supplies and DC-DC Converters

We have something
to whisper about...

TDK-Lambda



Latest Product News



Power Supply Highlights



QM – Series

First 1200 – 1500W rated modular series to have full MoPPs isolation, with 44,3 DBA the lowest acoustic noise at that power level and covered by an industry-leading 7-year warranty.

- Power: up to 1500W
- Output voltages: 2.8 to 105.6Vdc, wide range adjustable
- 1 to 16 Outputs + standby option
- EN55011/22 Class B (conducted and radiated)
- Full MoPPs isolation
- Suitable for B & BF applications



XMS500

New very flexible AC-DC power supply with medical approvals and up to 1792 combinations per output voltage.

- Power: 500W
- Output voltages: 12, 24 or 48Vdc
- Class I or Class II configurable power supply
- EN55011/22 Class B (conducted and radiated)
- Full MoPPs isolation
- Suitable for B, BF & CF applications



KWS-A – Series

Featuring a wide operating temperature range of up to 85°C and start-up temperatures of -40°C, the single output encapsulated power module series KWS-A is ideal for harsh industrial applications.

- Power: 5, 10, 15, 25W
- Output voltages: 5, 12, 15, 24Vdc
- Class II (no ground needed)



KMS-A – Series

Designed for medical and industrial applications that require robust, encapsulated, lightweight and compact power supplies, these sealed AC-DC pcb mount KMS-A supplies resist dust, and humidity.

- Power: 15, 30, 60W
- Output voltages: 5, 9, 12, 15, 24Vdc
- Class II (no ground needed)
- Operating Altitude 5.000m
- Suitable for B & BF applications



i6A – Series

250W Input Non-isolated DC-DC Converters

- Step-down (Buck) Converter
- 14A or 20A Positive Output or 8A Negative Output
- 1/16th brick Footprint
- Wide Output Adjustment : 3.3 to 24V, 3.3 to 15V, -3.3 to -30V
- Supports constant current applications



HQA – Series

120W Harsh Environment Quarter Brick DC-DC Converters

- 9 – 40V Wide Input
- 12 to 48V Nominal Outputs (5, 15V coming soon)
- -55°C to 115°C ambient temperatures
- No Opto-couplers used



RWS-B – Series

New 1000W/1500W AC-DC models. The high power density RWS-B series is featuring compact design, very long e-cap lifetime and warranty – an excellent balance of price vs performance.

- Power: 50, 100, 150, 300, 600, 1000, 1500W
- Output voltages: 5, 12, 15, 24, 36, 48Vdc
- Class B conducted & radiated EMI
- Operating temperature up to 70° C
- 7 year warranty



CUS-M – Series

New convection cooled AC-DC series with full medical approvals and low profile – ideal for applications where audible noise cannot be tolerated.

- Power: 150, 200, 350W
- Output voltages: 12, 18, 24, 36 or 48Vdc (15, 28Vdc coming soon)
- EN55011/22 Class B (conducted and radiated)
- Full MoPPs isolation
- Suitable for B & BF applications



DRB480

Single-phase 20A DIN Rail Mount Power – economic solution which combines very compact dimensions with high efficiency.

- Power: 480W
- Output voltages: 24Vdc
- Only 84mm wide
- Efficiency up to 93%
- 5 year warranty



DRL – Series

Very compact DIN Rail power supply with a low profile case – designed for building automation.

- Power: 10, 30, 60, 100W
- Output voltages: 12 or 24Vdc
- Class II
- ErP compliant



DRF960*

Single-phase 40A DIN Rail power supply which provides excellent efficiency – a reliable solution for many industrial applications.

- Power: 960W
- Output voltages: 24Vdc
- Only 110mm wide
- Efficiency up to 95%
- 5 year warranty

*coming soon

Power Supply Solutions.

Worldwide

TDK-Lambda offers a broad range of highly reliable power supplies worldwide.

Please contact us to see more power supply highlights – for all your power needs.



de.tdk-lambda.com



Please contact your local sales office to find the best solution to your application.



TDK-Lambda France SAS
3 avenue du Canada
Parc Technopolis – Bâtiment Sigma
91940 Les Ulis
France
Tel. +33 1 60 12 71 65
Fax +33 1 60 12 71 66
france@fr.tdk-lambda.com
www.fr.tdk-lambda.com



TDK-Lambda UK Ltd.
Kingsley Avenue
Ilfracombe
Devon EX34 8ES
United Kingdom
Tel. +44 12 71 85 66 66
Fax +44 12 71 86 48 94
powersolutions@uk.tdk-lambda.com
www.uk.tdk-lambda.com



Italy Sales Office
Via dei Lavoratori 128/130
20092 Cinisello Balsamo (MI)
Italy
Tel. +39 02 61 29 38 63
Fax +39 02 61 29 09 00
info.italia@it.tdk-lambda.com
www.it.tdk-lambda.com



TDK-Lambda Ltd.
Kibbutz
Givat Hashlosa 48800
Israel
Tel. +9 723 902 4333
Fax. +9 723 902 4777
info@tdk-lambda.co.il
www.tdk-lambda.co.il



Netherlands
info@nl.tdk-lambda.com
www.nl.tdk-lambda.com



TDK-Lambda Germany GmbH
Karl-Bold-Strasse 40
77855 Achern
Tel. +49 7841 666 0
Fax +49 7841 5000
info@de.tdk-lambda.com
www.de.tdk-lambda.com



C.I.S.
Commercial Support:
Tel. +7 495 665-26 27
Technical Support:
St. Petersburg
Tel. +7 812 658-04 63
info@tdk-lambda.ru
www.tdk-lambda.ru



Austria Sales Office
Aredstrasse 22
2544 Leobersdorf
Austria
Tel. +43 2256 655 84
Fax +43 2256 645 12
info@at.tdk-lambda.com
www.at.tdk-lambda.com



Nordic Sales Office
Haderslevvej 36B
6000 Kolding
Denmark
Tel. +45 2911 9656
info@dk.tdk-lambda.com
www.dk.tdk-lambda.com



Switzerland Sales Office
Bahnhofstrasse 50
8305 Dietlikon
Switzerland
Tel. +41 44 850 53 53
Fax +41 44 850 53 50
info@ch.tdk-lambda.com
www.ch.tdk-lambda.com

Local Distribution