



Ref. Certif. No.

DK-64643-A3-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

| | |
|---|---|
| Product | Switch mode power supply |
| Name and address of the applicant | TDK LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE DEVON EX34 8ES, UNITED KINGDOM |
| Name and address of the manufacturer | TDK LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE DEVON EX34 8ES, UNITED KINGDOM |
| Name and address of the factory | TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM |
| Note: <i>When more than one factory, please report on page 2</i> | |
| Ratings and principal characteristics | See Page 2 |
| Trademark / Brand (if any) | |
| Type of Customer's Testing Facility (CTF) Stage used | CTF Stage 3 |
| Model / Type Ref. | XMS Series. See Page 2 |
| Additional information (if necessary may also be reported on page 2) | The report was revised to include technical modifications <input checked="" type="checkbox"/> Additional Information on page 2 |
| A sample of the product was tested and found to be in conformity with | IEC 60950-1:2005/AMD1:2009, IEC 60950-1:2005/AMD2:2013, IEC 60950-1:2005 |
| As shown in the Test Report Ref. No. which forms part of this Certificate | E135494-A103-CB-2 issued on 2020-07-30 |

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-30
Original Issue Date: 2017-06-26

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-64643-A3-UL

Model Details:

XMS350 or XMS-350, XMS500 or XMS-500, XMS500P or XMS-500P, XMS500A or XMS-500A, XMS500AP or XMS-500AP series switch

See test report for details

Factories:

PANYU TRIO MICROTRONICS CO LTD

SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG 511453 CHINA

TRIO-TRONICS (THAILAND) LTD

7/295 MU. 6 MAP YANG PHON SUB-DISTRICT PLUAK DAENG DISTRICT RAYONG PROVINCE THAILAND

Ratings:

XMS350, XMS-350: 100-240Vac nom, 47-63Hz, 5.3A rms max.

XMS500, XMS-500, XMS500P, XMS-500P, XMS500A, XMS-500A,

XMS500AP, XMS-500AP: 100-240Vac nom, 47-63Hz, 7A rms max.

(see report Model Differences for details and variations)

Additional Information:

Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2: 2013; National Differences specified in the CB Test Report.

For Class II variants

The original report was modified to include the following changes/additions:

Models, ratings, list of critical components and factories revised. See test report for details.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-30

Original Issue Date: 2017-06-26

Signature:

Jan-Erik Storgaard