

# Achieving 250 watts in a noiseless 2" x 4" package

## CUS250M Series



- For medical & industrial applications
- Ultra-compact single output CUS250M power supplies provide excellent flexibility for easy design in and extraordinary standout features.

### First choice for system designers

- Maximum flexibility
- Impressive output power owing due to careful thermal management
- Silent operation with convection and conduction cooling
- High efficiency minimises running costs and environmental impact
- Worry free system integration due to significant EMI margins
- Flexible design-in with mechanical and signal options
- Ideal for medical and many other applications



Model	Output power	Output voltage	Input voltage	Size	Mechanical format	Cooling
CUS250M	250W	12, 15, 18, 24, 28, 36, 48Vdc	80 – 264Vac	2 x 4"	Open frame, baseplate, U-channel, enclosed, enclosed with top fan	



Product-Website



Product-Video



Data Sheet