

AC-DC Power Module
PFH500F-28 504W



TDK-Lambda

Points clés produit

- Design compact 2.4 x 4"
- Rendement jusqu'à 92%
- Idéal pour les systèmes refroidis par conduction
- Communication PMBus

Spécifications essentielles

- Sortie 28V ajustable de 22.4 - 33.6V
- Puissance de sortie de 504W
- Sortie auxiliaire 12V , partage du courant, DC Good
- Contrôle de la sortie via PMBus™ (lecture/écriture)

Applications typiques

- Alimentations sur mesure, Brick on Board
- Sources DC pour marchés COTS RF
- Equipements de télécommunication
- Signalisations et afficheurs LED

Product Highlights

- Compact 2.4 x 4" package
- Up to 92% efficient
- Suitable for conduction cooling
- PMBus™ communication

Key Specifications

- 28V output, adjustable from 22.4 - 33.6V
- 504W output power
- Current share, DC Good, 12V auxiliary
- Output control via PMBus™ (read/write)

Typical Applications

- Custom power supplies, Brick on Board
- COTS RF and DC power sources
- Outdoor communications equipment
- LED displays and signage