



TDK-Lambda

Aspectos Destacados

- Previene la pérdida de datos durante los cortes de tensión
- Condensadores electrolíticos para el almacenamiento de energía
- Sin baterías y suministra picos de energía

Especificaciones Clave

- 12, 15 o 24V de entrada y 20A de corriente nominal
- 380ms de hold-up time a 448W
- Encendido / apagado remoto para detener descargas no seguras
- Con capacidad de conexión en paralelo

Aplicaciones Típicas

- Semiconductor fabrication
- Process control
- Industrial machinery
- Test and measurement equipment

Product Highlights

- Prevents data loss during brief AC input losses
- Uses electrolytic capacitors to store energy
- No batteries to service or maintain
- Can also provide peak power capability

Key Specifications

- 20A current rating, 12, 15 or 24V input
- 380ms additional hold-up time at 448W
- Remote on/off to stop unsafe discharging
- Parallel capable

Typical Applications

- Semiconductor fabrication
- Process control
- Industrial machinery
- Test and measurement equipment