



## TDK-Lambda

### Points clés produit

- Contrôle du courant très rapide
- 7 modes de fonctionnement dont CC/CR/CP/CV
- Grand écran LCD en couleur de 89 mm
- Stocke et mémorise jusqu'à 8 paramètres

### Specifications essentielles

- Puissances nominales de 120 V (60 A/180 A) ou de 500 V (18 A/36 A)
- Possibilité de mise en parallèle jusqu'à 10 unités
- Hauteur de 3U, 300W demi-rack, 1000W rack complet
- Interface iEEE avec mesure d'ondulation en option

### Applications typiques

- Tests des équipements automatisés
- Laboratoires de R&D
- Testeurs de Batteries
- Testeurs d'alimentations électroniques

### Product Highlights

- High speed current control
- 7 operating modes including CC/CR/CP/CV
- Large 89mm colour LCD display
- Store and recall up to 8 memory settings

### Key Specifications

- 120V (60A/180A) or 500V (18A/36A) ratings
- Parallel capability of up to ten units
- 3U high, 300W half-rack, 1000W full-rack
- Optional iEEE interface and ripple measurement

### Typical Applications

- Automated Test Equipment
- R&D laboratories
- Battery testing
- Power supply testing