

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195
JAPAN

Name and address of the manufacturer

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195
JAPAN

Name and address of the factory

Note: When more than one factory, please report on page 2

WUXI TDK-LAMBDA ELECTRONICS CO LTD
NO 6 XING CHUANG ER LU WUXI JIANGSU 214028
CHINA Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)

TDK-Lambda

Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

ZWS50BAF-abcdef
a = 3, 5, 12, 15, 24, 48. b = "/" or blank. c = "A", "L" or blank.
d = "CO2" or blank. e = "FG" or blank. f = "FV" or blank.

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/ A11:2017.
National Differences specified in the CB Test Report. Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1(ed.2)

As shown in the Test Report Ref. No. which forms part of this Certificate

4788049709 issued on 2018-04-18

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-04-19

Signature:

Masamichi Takagi

Factories:

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI
MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN
MALAYSIA

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
TONGXIN RD ZHAOFENG ECONOMIC DEVELOPMENT ZONE LEYU TOWN ZHANGJIAGANG JIANGSU 215622
CHINA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831
JAPAN

Ratings:

Input: AC100-240V, 50/60Hz, 0.45A (for model ZWS50BAF-3), 0.67A (except for model ZWS50BAF-3)

Output :

DC3.3V, 10A ZWS50BAF-3
(DC2.64V-3.63V, max. 10A, max. 33.0W)
DC5V, 10A (ZWS50BAF-5)
(DC4.0V-5.5V, max. 10A, max. 50.0W)
DC12V, 4.3A (ZWS50BAF-12)
(DC9.6V-13.2V, max. 4.3A, max. 51.6W)
DC15V, 3.5A (ZWS50BAF-15)
(DC12.0V-16.5V, max. 3.5A, max. 52.5W)
DC24V, 2.1A (ZWS50BAF-24)
(DC19.2V-26.4V, max. 2.1A, max. 50.4W)
DC48V, 1.1A (ZWS50BAF-48)
(DC38.4V-52.8V, max. 1.1A, max. 52.8W)

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK



UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN



UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2018-04-19

Signature:

Masamichi Takagi