



## TDK·Lambda

## **Product Highlights**

- Ultracompact medical 4:1 input DC-DC converter (24 & 48V nom.)
- 5kVac isolation for 1 minute (defibrillator proof)
- 8mm spacing for 240Vac working voltage, 2 x MoPP
- 60601-1 3rd edition approval

## **Key Specifications**

- 3, 6 and 10 W industry standard DIP24 package
- Output voltages 3.3, 5, 12, 15, 24V DC and +/-5, +/-12, +/-15V DC
- Low patient leakage current < 0.25 μA</li>
- Remote on / off Positive logic and output trim functions

## **Typical Applications**

- Medical equipment
- Clinical care, Home medical
- Dentistry appliances
- Research laboratories