

**AC – DC medical adapter
DTM250- D 250W, Class I**



TDK-Lambda

Caratteristiche del prodotto

- Approvazioni medicali IEC/EN60601-1 (3rd Edition) & IEC/EN60601-1-2 (4th Edition)
- Isolamento ingresso uscita 4kV AC
- Corrente di contatto inferiore a 100µA
- Conforme alle normative DOE livello VI e EU

Caratteristiche principali

- 250W disponibili a seconda della tensione di uscita
- ampio range di ingresso 90 - 264VAC, connettore IEC60320-C14
- Modelli 12, 19, 24, 28, 36, 48 e 54 V DC
- Cavo di uscita a 4 pin DIN, o altre soluzioni disponibili

Applicazioni tipiche

- Attrezzature ospedaliere, dentistiche, cliniche e sanitarie
- Monitoraggio
- Imaging
- Applicazioni diagnostiche

Product Highlights

- Medical approval IEC/EN60601-1 (3rd Edition & IEC/EN60601-1-2 (4th Edition)
- Input to Output isolation 4kVAC
- Touch current less than 100µA
- Meets DOE level VI and EU Tier 2

Key Specifications

- 250W, depending on output voltage
- 90 – 264VAC wide input voltage, IEC60320-C14 connector
- 12, 19, 24, 28, 36, 48 and 54V DC models
- Output cable 4 pin DIN, others available

Typical Applications

- Hospital, Dental, Clinical and Healthcare Equipment
- Monitoring
- Imaging
- Diagnostic applications