

AC-DC Power Module  
PFH500F-28 504W



## TDK-Lambda

### Caratteristiche del prodotto

- Formato compatto 2,4 x 4"
- Efficienza fino al 92%
- Adatto per il raffreddamento a conduzione
- Interfaccia di comunicazione PMBus™

### Caratteristiche principali

- Tensione di uscita nominale 28V, regolabile da 22,4 a 33,6V
- Potenza di uscita 504W
- Current share, DC Good, 12V ausiliario
- Controllo dell'uscita tramite PMBus™ (read/write)

### Applicazioni tipiche

- Alimentatori custom, Brick on Board
- COTS RF and DC power sources
- Sistemi di comunicazione Outdoor
- Display e segnaletica a LED

### Product Highlights

- Compact 2.4 x 4" package
- Up to 92% efficient
- Suitable for conduction cooling
- PMBus™ communication

### Key Specifications

- 28V output, adjustable from 22.4 - 33.6V
- 504W output power
- Current share, DC Good, 12V auxiliary
- Output control via PMBus™ (read/write)

### Typical Applications

- Custom power supplies, Brick on Board
- COTS RF and DC power sources
- Outdoor communications equipment
- LED displays and signage