



TDK-Lambda

Caratteristiche del prodotto

- Formato standard industriale 2" x 1"
- Schermatura a sei lati
- Ampia gamma di tensioni di ingresso 4:1
- Ingresso on/off remoto
- Disponibili opzioni di montaggio del dissipatore di calore

Caratteristiche principali

- Potenza: 40W
- Tensioni di ingresso: 9 - 36Vdc o 18 - 75Vdc
- Tensione di isolamento I/O: 1600Vdc
- Efficienza: fino al 92%
- Uscite: 3.3V, 5V, 12V, 15V, 24V, 48V, $\pm 12V$, $\pm 15V$ or $\pm 24V$

Applicazioni tipiche

- Apparecchiature portatili
- Industria
- Laboratorio, misurazioni e test
- Telecomunicazioni
- Elaborazione dati

Product Highlights

- 2 x 1" Industry standard size
- Six sided shielding
- 4:1 Wide input voltage range
- Remote on/off input
- Fitted heat sink options available

Key Specifications

- Power: 40W
- Input voltage: 9 - 36Vdc or 18 - 75Vdc
- Isolation voltage I/O: 1600Vdc
- Efficiency: up to 92%
- Output: 3.3V, 5V, 12V, 15V, 24V, 48V, $\pm 12V$, $\pm 15V$ or $\pm 24V$

Typical Applications

- Mobile equipment
- Industry
- Laboratory, measurement and testing
- Telecommunications
- Data processing