



TDK-Lambda

Caratteristiche del prodotto

- Formato quarter brick standard industriale 2.28x1.45"
- Certificazione EN 50155 per applicazioni ferroviarie
- Ampia gamma di tensioni di ingresso 8:1
- Ingresso on/off remoto
- Numerose funzioni di autoprotezione

Caratteristiche principali

- Potenza: 75W
- Tensione di ingresso: 9 - 75Vdc
- Uscite: 12V, 15V, 24V, 28V or 48V
- Tensione di isolamento I/O: 3000Vac
- Efficienza: fino al 90%

Applicazioni tipiche

- Ferroviario e trasporti
- Industria
- Laboratorio, misurazioni e test
- Telecomunicazioni
- Elaborazione dati

Product Highlights

- Quarter brick industry standard 2.28 x 1.45"
- EN 50155 – Suitable for railway applications
- 8:1 Ultra-wide input voltage range
- Remote on/off input
- Extensive protection functions

Key Specifications

- Power: 75W
- Input voltage: 9 - 75Vdc
- Output: 12V, 15V, 24V, 28V or 48V
- Isolation voltage I/O: 3000Vac
- Efficiency: up to 90%

Typical Applications

- Railway and Transportation
- Industry
- Laboratory, measurement and testing
- Telecommunication
- Data processing