

AC – DC Power Supplies
TPS4000 4kW 3-Phase Input



TDK-Lambda

Caratteristiche del prodotto

- Ingresso 400/440/480Vac (nominale) trifase Delta o Wye
- Programmazione remota di tensione e corrente
- FET ORing incorporato per funzionamento in parallelo
- Comunicazione PMBus™

Caratteristiche principali

- Potenza di uscita fino a 4080W
- Ampia gamma di potenza di uscita 24V e 48V regolabili
- 92% di efficienza
- Da -40°C (start up) a +70°C

Applicazioni tipiche

- Macchine da stampa digitali
- Trasmissione RF
- Apparecchiature di test di semiconduttori
- Additive manufacturing (stampanti 3D)

Product Highlights

- 400/440/480Vac (nominal) input 3-phase Delta or Wye
- Remote voltage and current programming
- Built in ORing FET for parallel operation
- PMBus communication

Key Specifications

- Up to 4080W output power
- Wide range adjustable 24V and 48V outputs
- 92% typical efficiency
- -40°C (start up) to +70°C operation

Typical Applications

- Digital printing presses
- RF transmission
- Semiconductor test equipment
- Additive manufacturing (3D printing)