



TDK-Lambda

Caratteristiche del prodotto

- Convertitore step-down (Buck) non isolato con uscita negativa
- 8A (75W) POL alta densità
- Alta efficienza fino al 94%
- 1/16o di brick
- Temperatura di esercizio da -40 a +125°C con minima riduzione di potenza

Caratteristiche principali

- Tensione d'ingresso da 9 a 40Vdc
- Tensione d'uscita regolabile da -3.3 a -30Vdc
- Sensing remoti
- Garanzia 3 anni

Applicazioni tipiche

- Fornisce la conversione da un bus 12V o 24V
- Mercati di riferimento:
Industriale generale
Test & Misurazioni
Medicale
Broadcast

Product Highlights

- Step-down (Buck) non-isolated converter with negative output
- 8A (75W) high density POL
- High efficiency up to 94%
- 1/16th brick footprint
- Operating temp. -40 to +125°C with minimal power derating

Key Specifications

- 9 to 40Vdc input range
- -3.3 to -30Vdc adjustable output
- Remote sense
- 3 years warranty

Typical Applications

- Local conversion from 12V or 24V Bus
- Target markets:
General Industrial
Test and Measurement
Medical
Broadcast