

Certificate



Certificate no.

TA 50317859 01

License Holder:

TDK-Lambda Americas Inc.
401 Mile of Cars Way, Suite 325,
National City, CA 91950
USA

Manufacturing Plant:

Original license holder
331792
Power-Win Technology Corp.

Test report no.: ZTW1- 10043565 003

Client Reference: KW-20150616-A12&OEM

Tested to: IEC 60601-1:2005
EN 60601-1:2006+A11+A12

Certified Product: (AC Power Adapter)

License Fee - Units

Type Designation	: DTM65PWXXXC8-ZZZ (TDK-Lambda)	1
XXX stands for	: 050, 120, 150, 190, 240, 280, 480	1
Z stands for	: A-Z, 0-9 or blank	1
Rated Voltage	: AC 100-240V, 50-60Hz	
Rated Current	: 2-1A	
Output Voltage	: see Appendix	
Output Current	: see Appendix	
max. Ambient Temperature	: 40°C	
Protection Class	: II	

Remark: 1. This risk management requirements of the standard were not addressed.
2. This certificate is valid for maximum 5 years.

3

Licensed Test mark:



TÜV Rheinland Taiwan Ltd.



Signature

Dipl.-Ing. F. Stölzel

**Date of Issue
(day/mo/yr)**

06/08/2015

Appendix to TÜV approved Certificate No.: TA 50317859

Certified Product : AC Power Adapter
Report Number : 10043565 003
Type Designation : DTM65PWXXXC8-ZZZ
(XXX = 050, 120, 150, 190, 240, 280, 480; Z = A-Z, 0-9 or blank)

Model TDK-Lambda	Rating		
	Output Voltage	Output Current	Max. Output Power
DTM65PW050C8-ZZZ	5	8	40
DTM65PW120C8-ZZZ	12	5	60
DTM65PW150C8-ZZZ	15	4	60
DTM65PW190C8-ZZZ	19	3.42	65
DTM65PW240C8-ZZZ	24	2.7	65
DTM65PW280C8-ZZZ	28	2.32	65
DTM65PW480C8-ZZZ	48	1.35	65

Date: 06th August, 2015

Certification Body

A blue ink signature of F. Stoelzel is written over the text 'Certification Body' and 'Dipl.-Ing. F. Stoelzel'.

Dipl.-Ing. F. Stoelzel