



TDK-Lambda

Produkt-Merkmale

- 2 x 1" Abmessung im Industrieformat
- Allseitig geschirmt
- 4:1 Weiter Eingangsspannungsbereich
- Remote Ein/Aus Steuereingang
- Passende Kühlkörper optional verfügbar

Spezifikationen

- Leistung: 60W
- Eingangsspannung: 9 - 36Vdc oder 18 - 75Vdc
- Isolationsspannung I/O: 1600Vdc
- Wirkungsgrad: bis zu 92%
- Ausgang: 3.3V, 5V, 12V, 15V, 24V, $\pm 12V$, $\pm 15V$ oder $\pm 24V$

Typische Einsatzbereiche

- Mobile Geräte
- Industrie
- Labor, Mess- und Prüftechnik
- Telekommunikation
- Datenverarbeitung

Product Highlights

- 2 x 1" Industry standard size
- Six sided shielding
- 4:1 Wide input voltage range
- Remote on/off input
- Fitted heat sink options available

Key Specifications

- Power: 60W
- Input voltage: 9 - 36Vdc or 18 - 75Vdc
- Isolation voltage I/O: 1600Vdc
- Efficiency: up to 92%
- Output: 3.3V, 5V, 12V, 15V, 24V, $\pm 12V$, $\pm 15V$ or $\pm 24V$

Typical Applications

- Mobile equipment
- Industry
- Laboratory, measurement and testing
- Telecommunications
- Data processing