

AC - DC 70W Medical Adapter
DTM70 Series



TDK-Lambda

Points clés produit

- Homologation médicale IEC/EN/UL60601-1 ED:3 pour les applications 2x MOPP
- Modèles de classe de protection I (DTM70) et de classe II (DTM70-C8) disponibles
- IEC/EN/UL60601-1 -11 pour DTM70-C8
- Conformité ErP et niveau de rendement DoE VI

Specifications essentielles

- Modèles 12, 24, 36 et 48V DC
- Fonctionne jusqu'à 5000m d'altitude
- Large plage d'entrée AC 100-240V
- Aucune perte de charge <150mW
- Connecteur de sortie verrouillable

Applications typiques

- Équipement hospitalier, dentaire, clinique et de soins à domicile
- Équipement de surveillance
- Matériel d'imagerie et de diagnostic
- Applications industrielles

Product Highlights

- Medical approval IEC/EN/UL60601-1 ED:3 for 2x MOPP applications
- Protection class I (DTM70) and Class II (DTM70-C8) models available
- IEC/EN/UL60601-1 -11 for DTM70-C8
- ErP compliant and DoE efficiency level VI

Key Specifications

- 12, 15, 18, 24, 36 and 48V DC models
- Altitude up to 5000m
- AC 100-240V Wide-range input
- No load losses <150mW
- Locking output connector

Typical Applications

- Hospital, dental, clinical and home healthcare equipment
- Monitoring equipment
- Imaging and diagnostic equipment
- Industrial applications