

**1500W AC-DC PFC Module**  
**PF1500B series - 360V output**



## TDK-Lambda

### Points clés produit

- Convient aux fournitures personnalisées
- Température de la plaque de base jusqu'à 100 °C
- Refroidi par conduction via une plaque de base
- Entièrement équipé avec signalisation et marche/arrêt à distance

### Specifications essentielles

- Sortie de 1,5 kW à 230 Vac, 1 kW à l'entrée de 115 Vac
- Rendement jusqu'à 96,5 %
- Encombrement 1 brique
- Fonctionnement en parallèle jusqu'à 3 unités

### Applications typiques

- Systèmes d'alimentation personnalisés
- Architectures de puissance distribuée haute tension
- Fabrication de semi-conducteurs
- Test et mesure

### Product Highlights

- Suitable for custom supplies
- Up to 100°C rated baseplate temperature
- Conduction cooled via baseplate
- Fully featured with signalling & remote on/off

### Key Specifications

- 1.5kW output at 230Vac, 1kW at 115Vac input
- Up to 96.5% efficient
- Compact full brick package
- Parallel operation with up to 3 units

### Typical Applications

- Custom power systems
- High voltage distributed power architectures
- Semiconductor fabrication
- Test and measurement