

AC-DC Power Supplies QS5 and QS7 (600-1200W)



TDK-Lambda

Points clés produit

- Faible bruit acoustique
- Multiples options de contrôle et de mise en veille
- Adapté aux applications industrielles et médicales
- Isolation électrique conforme BF

Spécifications essentielles

- Puissance de sortie 600-1200W
- Entrée universelle 90 – 264VAC
- Modèles en sortie 12, 24 et 48V DC
- PMBus™ en option

Applications typiques

- Instrumentation
- Télédiffusion, radiodiffusion
- Médical (hôpitaux, dentaire, soins, monitoring, imagerie)
- Contrôle qualité

Product Highlights

- Low audible noise
- Various standby and control options available
- Suitable for Industrial and Medical applications
- BF ready medical isolation

Key Specifications

- 600-1200W output power
- 90 – 264VAC wide input voltage
- 12, 24 or 48V DC outputs
- PMBus™ option available

Typical Applications

- Test and measurement
- Broadcast
- Healthcare (hospital, dental, clinical, monitoring, imaging)
- Diagnostic applications

For more information about TDK-Lambda: www.emea.tdk-lambda.com