



Product Service

# CERTIFICATE

No. B 109510 0001 Rev. 00

**Holder of Certificate:** TDK-Lambda UK Limited  
Kingsley Avenue  
Ilfracombe, Devon, EX34 8ES  
UNITED KINGDOM

**Certification Mark:**



**Product:** Power supplies  
( AC-DC Din Rail Mountable Power Supplies )

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: [www.tuvsud.com/ps-cert](http://www.tuvsud.com/ps-cert)

**Test report no.:** 6121020056401

**Valid until:** 2024-06-17

**Date,** 2020-09-23

( Owen Hsu )



Product Service

# CERTIFICATE

No. B 109510 0001 Rev. 00

**Model(s):** DSP10-5, DSP10-12,  
DSP10-15, DSP10-24

**Brand Name:** TDK-Lambda

## TDK-Lambda

**Parameters:** Rated inputs: See below  
Rated outputs: See below  
Protection class: II  
Max. ambient temperature: 55 °C

**Remarks:**

1. When installing, all requirements of below mentioned test standards must be fulfilled.
2. The equipment is evaluated for operating in altitude up to 5,000 m above the sea level.

The ratings & model description of the models are as below:

Model-#	Input Rating	Output Voltage	Output Current	Output Power
DSP10-5	100-240 Vac, 47-63 Hz, 300 mA	5 Vdc	1.5 A	7.5 W
DSP10-12		12 Vdc	0.83 A	10 W
DSP10-15		15 Vdc	0.67 A	10 W
DSP10-24		24 Vdc	0.42 A	10 W

**Tested according to:** EN 62368-1:2014

**Production Facility(ies):** 004727, 004978

ZERTIFIKAT ◆ CERTIFICATE ◆ 認 證 證 書 ◆ CERTIFICADO ◆ CERTIFICAT