



TDK-Lambda

Points clés produit

- Encombrement standard de l'industrie 2,28x1,45"
- EN 50155 – Convient aux applications ferroviaires
- Plage de tension d'entrée ultra-large 12:1
- Entrée marche/arrêt à distance
- Fonction de protection étendue

Specifications essentielles

- Puissance : 50W
- Tension d'entrée : 14 - 160Vdc
- Sortie : 5V, 12V, 24V ou 28V
- Tension d'isolation E/S : 3000Vdc
- Efficacité : jusqu'à 89 %

Applications typiques

- Ferroviaire et transport
- Industrie
- Laboratoire, mesures et test
- Télécommunication
- Traitement de données

Product Highlights

- Quarter brick industry standard 2.28 x 1.45"
- EN 50155 – Suitable for railway applications
- 12:1 Ultra-wide input voltage range
- Remote on/off input
- Extensive protection functions

Key Specifications

- Power: 50W
- Input voltage: 14 - 160Vdc
- Output: 5V, 12V, 24V or 28V
- Isolation voltage I/O: 3000Vdc
- Efficiency: up to 89%

Typical Applications

- Railway and Transportation
- Industry
- Laboratory, measurement and testing
- Telecommunication
- Data processing