



TDK-Lambda

Points clés produit

- Taille standard de l'industrie 2,28 x 1,45"
- EN 50155 - Convient aux applications ferroviaires
- Plage de tension d'entrée ultra-large 8:1
- Entrée marche/arrêt à distance
- Fonctions de protection étendues

Specifications essentielles

- Puissance : 75W
- Tension d'entrée : 9 - 75Vdc
- Sortie : 12V, 15V, 24V, 28V ou 48V
- Tension d'isolement E/S : 3 000 Vac
- Efficacité : jusqu'à 90 %

Applications typiques

- Équipement mobile
- Industrie
- Laboratoire, test et mesures
- télécommunications
- Traitement de données

Product Highlights

- Quarter brick industry standard 2.28 x 1.45"
- EN 50155 – Suitable for railway applications
- 8:1 Ultra-wide input voltage range
- Remote on/off input
- Extensive protection functions

Key Specifications

- Power: 75W
- Input voltage: 9 - 75Vdc
- Output: 12V, 15V, 24V, 28V or 48V
- Isolation voltage I/O: 3000Vac
- Efficiency: up to 90%

Typical Applications

- Railway and Transportation
- Industry
- Laboratory, measurement and testing
- Telecommunication
- Data processing