



TDK-Lambda

Produkt-Merkmale

- Quarter-Brick Industrieformat 2,28" x 1,45"
- EN 50155 - geeignet für Bahnanwendungen
- 8:1 Ultraweiter Eingangsspannungsbereich
- Remote Ein/Aus Steuereingang
- Umfangreiche Schutzfunktionen

Spezifikationen

- Leistung: 75W
- Eingangsspannung: 9 - 75Vdc
- Ausgang: 12V, 15V, 24V, 28V oder 48V
- Isolationsspannung I/O: 3000Vac
- Wirkungsgrad: bis zu 90%

Typische Einsatzbereiche

- Bahn und Transportwesen
- Industrie
- Labor, Mess- und Prüftechnik
- Telekommunikation
- Datentechnik

Product Highlights

- Quarter brick industry standard 2.28 x 1.45"
- EN 50155 – Suitable for railway applications
- 8:1 Ultra-wide input voltage range
- Remote on/off input
- Extensive protection functions

Key Specifications

- Power: 75W
- Input voltage: 9 - 75Vdc
- Output: 12V, 15V, 24V, 28V or 48V
- Isolation voltage I/O: 3000Vac
- Efficiency: up to 90%

Typical Applications

- Railway and Transportation
- Industry
- Laboratory, measurement and testing
- Telecommunication
- Data processing