



Test Report issued under the responsibility of:



<b>IEC 60601-1</b> <b>Medical electrical equipment</b> <b>Part 1: General requirements for basic safety and essential performance</b>	
Report Reference No. ....	E349607-D1006-1/A1/C0-CB
Date of issue .....	2017-11-16; 2017-12-18 (A1)
Total number of pages .....	149
CB Testing Laboratory .....	UL International Germany GmbH Admiral Rosendahl Strasse 23 63263 Zeppelinheim/Neu-Isenburg Germany
Applicant's name .....	TDK-Lambda UK LTD Kingsley Avenue Ilfracombe, EX34 8ES UK
Test specification:	
Standard .....	IEC 60601-1:2005 (Third Edition) + CORR. 1:2006 + CORR. 2:2007 + A1:2012 (or IEC 60601-1: 2012 reprint)
Test procedure .....	CB Scheme
Non-standard test method.....	N/A
Test Report Form No.....	IEC60601_1K
Test Report Form Originator .....	UL(US)
Master TRF .....	2015-11
Copyright © 2015 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved. This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context. This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.	
<b>General disclaimer:</b> The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB testing laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.	

Test item description:	Switch mode modular power supplies for installation into medical equipment	
Trade Mark:	TDK-Lambda	
Manufacturer:	Same as Applicant	
Model/Type reference:	CM4	
Ratings:	CM4 input rating: 100-240 V ac nom, 7A rms max, 50-60Hz or 120-370 V dc, 7A max  Output power is 600 W max  Individual outputs rated according to modules fitted.  Output modules ratings (rated output voltage marked on the device can be any values within the ranges specified below): S1 = 1.5 - 7.5Vdc, 25A, 125W S2 = 4.5 - 15Vdc, 15A, 150W S3 = 9 - 30Vdc, 7.5A, 150W S4 = 18 - 58Vdc, 3.75A, 150W  All output modules current and power ratings are the maximum allowable.	
Testing procedure and testing location:		
<input checked="" type="checkbox"/> CB Testing Laboratory:		
Testing location/ address:	UL International Germany GmbH Admiral Rosendahl Strasse 23 63263 Zeppelinheim/Neu-Isenburg Germany	
<input type="checkbox"/> Associated CB Testing Laboratory:		
Testing location/ address:		
Tested by (name, function, signature):	Krzysztof Wasilewski (Project Handler)	<i>Krzysztof Wasilewski</i>
Approved by (name, function, signature):	Jakub Sobolewski (Project Reviewer)	<i>Jakub Sobolewski</i>
Testing procedure: CTF Stage 1:		
Testing location/ address:		
Tested by (name, function, signature):		
Approved by (name, function, signature):		
Testing procedure: CTF Stage 2		
Testing location/ address:		
Tested by (name, function, signature):		

Witnessed by (name, function, signature):		
Approved by (name, function, signature):		
<hr/>		
<input type="checkbox"/> Testing procedure: CTF Stage 3:		
<input type="checkbox"/> Testing procedure: CTF Stage 4:		
Testing location/ address:		
Tested by (name, function, signature):		
Witnessed by (name, function, signature):		
Approved by (name, function, signature):		
Supervised by (name, function, signature):		
<hr/>		

List of Attachments (including a total number of pages in each attachment):

Refer to Appendix A of this report. All attachments are included within this report.

Summary of testing

Tests performed (name of test and test clause):

Testing location:

*Refer to the Test List in Appendix D of this report if testing was performed as part of this evaluation.*

Summary of compliance with National Differences

List of countries addressed: Austria, Korea, Republic of, USA, Canada, United Kingdom, Sweden

[X] The product fulfils the requirements of IEC 60601-1:2005 (Third Edition) + CORR. 1:2006 + CORR. 2:2007 + A1:2012

(or IEC 60601-1: 2012 reprint).

Copy of marking plate

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.

*Refer to the enclosure(s) titled Marking Label in the Enclosures section in Appendix A of this report for a copy.*

GENERAL INFORMATION	
Test item particulars (see also Clause 6):	
Classification of Installation and Use:	Component part of host equipment
Device type (component/sub-assembly/ equipment/ system):	Component Switch Mode Power Supply
Intended use (Including type of patient, application location):	To supply regulated power to medical equipment
Mode of Operation:	Continuous
Supply Connection:	Connection to mains via host equipment
Accessories and detachable parts included:	None
Other Options Include:	
Testing	
Date of receipt of test item(s) .....	2016-04-20, 2016-06-21, 2016-10-21, 2016-08-23, 2016-10-17, 2017-09-27, N/A (A1)
Dates tests performed .....	2016-10-04 to 2016-11-30, 2017-10-03 to 2017-10-16, N/A (A1)
Possible test case verdicts:	
- test case does not apply to the test object .....	N/A
- test object does meet the requirement.....	Pass (P)
- test object was not evaluated for the requirement .....	N/E
- test object does not meet the requirement.....	Fail (F)
Abbreviations used in the report:	
- normal condition: N.C.	- single fault condition: S.F.C.
- means of Operator protection: MOOP	- means of Patient protection: MOPP
General remarks:	
<p>Before starting to use the TRF please read carefully the 4 instructions pages at the end of the report on how to complete the new version "K" of TRF for IEC for 60601-1 3rd edition with Amendment 1.</p> <p>"(See Attachment #)" refers to additional information appended to the report.</p> <p>"(See appended table)" refers to a table appended to the report.</p> <p>The tests results presented in this report relate only to the object tested.</p> <p>This report shall not be reproduced except in full without the written approval of the testing laboratory.</p> <p>List of test equipment must be kept on file and available for review.</p> <p>Additional test data and/or information provided in the attachments to this report.</p> <p>Throughout this report a point is used as the decimal separator.</p>	
Manufacturer's Declaration per sub-clause 4.2.5 of IEC 60601-1:2012	
The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided .....	Yes
When differences exist; they shall be identified in the General product information section.	

Name and address of factory (ies) .....: Same as Applicant

Panyu Trio Microtronics Co. Ltd.  
SHIJI INDUSTRIAL ESTATE, DONGYONG,  
NANSHA, GUANGZHOU  
GUANGDONG 511453 CHINA

## GENERAL PRODUCT INFORMATION:

### Report Summary

All applicable tests according to the referenced standard(s) have been carried out.  
Refer to the Report Modifications for any modifications made to this report.

### Product Description

CM4 is an AC/DC switch mode power supply series. The device uses fan-less, modular architecture based on selection of output modules. Unit can be configured with up to four output modules (in parallel / series combinations) that determine output ratings. The total output power is 600W (for de-ratings see additional information). Equipment is open-frame, uses metal baseplate and is intended for building-in to the host equipment.

The CM4 switch mode power supply consists of:

1. Input filter board and power conversion board (PRIMARY)
2. Planar transformer (PRI/SEC)
3. Output modules (SECONDARY)

### Model Differences

N/A

### Additional Information

CM4 Part No details:

CM4 xZ xY xY xY [opt] [fact]

Where x = Output voltage of the module fitted

Where Z = Module fitted in the slot

Where Y = Optional module (depending on total number of slots) or O for not fitted

Where [opt] can be blank or -IN for power supply inhibit or -EN for power supply enable

Where [fact] (for factory option) can be blank for standard unit or -xxx where xxx is any combination of letters or numbers for non-safety related modifications.

The CM4 Series switch mode power supply can be configured in the following variations:

Sx = Single output S1, S2, S3, S4 as per table below

Zx = Modules S1, S2, S3 or S4 connected in parallel as per table below

Yx = Modules S1, S2, S3 or S4 connected in series as per table below

Hx = Modules S1, S2, S3 or S4 are combined (series connection of parallel connected modules) as per table below.

Where "x" can be any alphanumeric character

Module	#Slots	Output voltage range	Nominal Voltage	Output current	Rated Power
S1	1	1.5Vdc - 7.5Vdc	5Vdc	25A	125W

Z1	2	1.5Vdc - 7.5Vdc	5Vdc	50A	250W
ZA	3	1.5Vdc - 7.5Vdc	5Vdc	75A	375W
ZN	4	1.5Vdc - 7.5Vdc	5Vdc	100A	500W
Y1	2	3Vdc - 15Vdc	10Vdc	25A	250W
HA	4	3Vdc - 15Vdc	10Vdc	50A	500W
S2	1	4.5Vdc - 15Vdc	12Vdc	15A	150W
Z2	2	4.5Vdc - 15Vdc	12Vdc	30A	300W
YA	3	4.5Vdc - 22.5Vdc	15Vdc	25A	375W
ZB	3	4.5Vdc - 15Vdc	12Vdc	45A	450W
ZP	4	4.5Vdc - 15Vdc	12Vdc	60A	600W
YN	4	6Vdc - 30Vdc	20Vdc	25A	500W
S3	1	9Vdc - 30Vdc	24Vdc	7.5A	150W
Y2	2	9Vdc - 30Vdc	24Vdc	15A	300W
ZC	3	9Vdc - 30Vdc	24Vdc	22.5A	450W
HB	4	9Vdc - 30Vdc	24Vdc	30A	600W
ZQ	4	9Vdc - 30Vdc	24Vdc	30A	600W
YB	3	13.5Vdc - 45Vdc	36Vdc	15A	450W
S4	1	18Vdc - 58Vdc	48Vdc	3.75A	150W
Y3	2	18Vdc - 60Vdc	48Vdc	7.5A	300W
ZD	3	18Vdc - 58Vdc	48Vdc	11.25A	450W
ZR	4	18Vdc - 58Vdc	48Vdc	15A	600W
YP	4	18Vdc - 60Vdc	48Vdc	15A	600W
YC	3	27Vdc - 90Vdc	72Vdc	7.5A	450W
Y4	2	36Vdc - 116Vdc	96Vdc	3.75A	300W
YQ	4	36Vdc - 120Vdc	96Vdc	7.5A	600W
YD	3	54Vdc - 174Vdc	144Vdc	3.75A	450W
YR	4	72Vdc - 232Vdc	192Vdc	3.75A	600W

Input Parameters:

Nominal input voltage 100 – 240 Vac (or 120 – 370 V dc)

Input voltage range 85 – 264 Vac (or 120 – 370 V dc)

Input frequency range 50 – 60 Hz

Maximum input current 7 A rms (fuse 8 A)

The total output power is 600 W from output modules plus 5 W bias power from J5-Global connector (5 V dc, 1 A).

The following power deratings are applicable:

a. Line voltages <120 V ac:

600 W @ 120 V ac to 425 W @ 85 V ac (linear, applies to input and output power)

b. baseplate temperatures > 85°C:

600 W @ 85°C TO 300 W @ 105°C (linear, applies to output power and bias power)

Baseplate temperature shall be measured on the TS1 reference point defined in the Diagram-01 (see Enclosures).



c. ambient temperatures > 50°C:

600 W @ 50°C to 300 W @ 70°C (linear, applies to input power)

Line deratings and temperature deratings are cumulative.

### Technical Considerations

- The product was investigated to the following standards:

#### Main Standard(s):

ANSI/AAMI ES60601-1: A1:2012, C1:2009/(R)2012 and A2:2010/(R)2012, CSA CAN/CSA-C22.2 NO. 60601-1:14, IEC 60601-1 Edition 3.1 (2012)

#### From Country Differences:

- Austria: EN 60601-1:2006/A1:2013
- Korea, Republic of: KS C IEC 60601-1
- USA: ANSI/AAMI ES60601-1: A1:2012, C1:2009/(R)2012 and A2:2010/(R)2012
- Canada: CSA CAN/CSA-C22.2 NO. 60601-1:14
- United Kingdom: BS EN 60601:2006 A1
- Sweden: SS-EN 60601-1:2006+A11:2011+A1:2013+AC1:2014+A12:2014

#### Additional Standards:

EN 60601-1:2006/ A11:20011/ A1:2013/ A12:2014

- The following additional investigations were conducted: N/A
- The product was not investigated to the following standards or clauses: Biocompatibility, PESS, EMC, Annex Z of EN standards for compliance with the MDD
- The following accessories were investigated for use with the product: N/A
- No Other Considerations.

### Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

The following production line tests are conducted for this product: Electric Strength, Earthing Continuity

The following secondary output circuits are at hazardous energy levels: output modules S2, S3.

The following secondary output circuits are non-hazardous energy levels: S1, S4, J5-Global bias, J5-Output bias.

The following output terminals were referenced to earth during performance testing. All outputs and their return lines individually referenced to earth to obtain maximum working voltage.

The power supply terminals and/or connectors are: not investigated for field wiring

The maximum investigated branch circuit rating is: 20 A

The investigated pollution degree is: II

Proper bonding to the end product main protective earthing termination is: required

The following end-product enclosures are required: Mechanical, Fire, Electrical

The product was tested for use at the maximum ambient temperature (TMA) 70° C (with deratings above

50°C – see additional information for details)

An investigation of the protective bonding terminals has been conducted

EMC compliance has not been verified nor has it been taken into consideration. An accredited EMC Test Report will be required in conjunction with the Certification of the end product.

The product was evaluated for use at the maximum altitude of operation: 3000 m

Component power supply, risk management requirements of the standard were not addressed, to be considered as part of end-product. refer to OD 2055:2015 for further details.

The marking requirements of Clauses 7.2, 7.3 & 7.5 must be considered in the end product application.

#### Report Modifications

Date Modified (Year-Month-Day)	Modifications Made (include Report Reference Number)	Modified By
2017-12-18	Amendment to the report to add non safety related options [opt] and [fact] to unit configuration description in the additional information section of this report. Equipment construction remains unchanged. No testing was considered necessary to make this change. The report must be read in conjunction with the original CB Test Report Ref. No. E349607-D1006-1/A0/C0-CB and CB Test Certificate No. dK-68252-UL issued 2017-11-17.	Krzysztof Wasilewski