


## 40W Single and Dual Output DC-DC converters


<https://product.tdk.com/en/power/pxd>  
[www.emea.lambda.tdk.com/pxd](http://www.emea.lambda.tdk.com/pxd)



The PXD40 industrial DC-DC converters feature wide 4:1 input ranges in a compact 2 x 1" (50.8 x 25.4mm) industry standard package. With efficiencies up to 93%, the PXD40 series typically draws a low 3mA input current when the remote on/off function is used, prolonging battery life for portable equipment. The modules have six-sided shielding to reduce radiated noise.

Features	Benefits
• Wide 4:1 Input Range	• Supports Dual 12/24V or 24/48V System Voltages
• Compact 2" x 1" Industry Package	• Less Board Area Needed
• Certified to IEC/UL/CSA/EN 62368-1	• Suitable For Industrial Applications
• Low No Load Power Consumption	• Longer Battery Life
• Six Sided Shielding	• Reduces Radiated Noise

Model Selector							
Model	Input Voltage (V)	Output Voltage (V)	Maximum Current (A)	Maximum Power (W)	No Load Input Current (mA)	Efficiency (%)	Maximum Load Capacitance (uF)
<b>Single Outputs</b>							
PXD40-24WS3P3	9 - 36	3.3	12.2	40.3	15	89.5	22,000
PXD40-48WS3P3	18 - 75	3.3	12.2	40.3	10	90	22,000
PXD40-24WS05	9 - 36	5	8	40	15	92	12,000
PXD40-48WS05	18 - 75	5	8	40	10	91	12,000
PXD40-24WS12	9 - 36	12	3.333	40	15	92	2,000
PXD40-48WS12	18 - 75	12	3.333	40	10	92	2,000
PXD40-24WS15	9 - 36	15	2.666	40	15	93	1,300
PXD40-48WS15	18 - 75	15	2.666	40	10	92	1,300
PXD40-24WS24	9 - 36	24	1.666	40	15	91	490
PXD40-48WS24	18 - 75	24	1.666	40	10	92	490
PXD40-24WS48	9 - 36	48	0.833	40	15	91	120
PXD40-48WS48	18 - 75	48	0.833	40	10	92	120
<b>Dual Outputs</b>							
PXD40-24WD12	9 - 36	±12	±1.666	40	15	91	±980
PXD40-48WD12	18 - 75	±12	±1.666	40	10	91	±980
PXD40-24WD15	9 - 36	±15	±1.333	40	15	91	±630
PXD40-48WD15	18 - 75	±15	±1.333	40	10	91	±630
PXD40-24WD24	9 - 36	±24	±0.833	40	15	91	±250
PXD40-48WD24	18 - 75	±24	±0.833	40	10	92	±250



Preferred model

## Related Products

Type	Part Number	Description
Heatsink kit (User installation)	ACC-PX2X1-HC01	HC1 heatsink, thermal pad and 2 clips
Heatsink kit (User installation)	ACC-PX2X1-HC02	HC2 heatsink, thermal pad and 2 clips
Heatsink kit (User installation)	ACC-PX2X1-HC03	HC3 heatsink, thermal pad and 2 clips

## Specifications

Model	PXD40	
<b>Input</b>		
Input Voltage Range	-	See model selector table
Input Surge Voltage	Vdc	-24W models: 50, -48W models: 100. (1s maximum)
Input Shutdown Voltage	Vdc	-24W models: 7 - 8.8, -48W models: 15 - 17.5
Start-up Time	ms	60 max
No Load Current Consumption	mA	See model selector table. Typically 3 when remote on/off is activated
Efficiency	-	See model selector table
Conducted & Radiated EMI	-	EN55032. See instruction manual on website for external circuitry
Immunity	-	See immunity section
Safety Certifications and Markings	-	IEC/UL/CSA/EN62368-1, CE Mark and UKCA Mark

## Immunity

Test	Standard	Test Level	Criteria	Notes
ESD	EN61000-4-2	Air $\pm 8$ kV and Contact $\pm 6$ kV	A	-
Radiated Susceptibility	EN61000-4-3	10V/m	A	-
Electrical Fast Transient Burst	EN61000-4-4	$\pm 2$ kV	A	With an input filter of two 220uF capacitors and a TVS (SMDJ58A for PXD40-24W or SMDJ120A for PXD40-48W)
Surge	EN61000-4-5	$\pm 2$ kV	A	
Conducted Susceptibility	EN61000-4-6	10 Vrms	A	-
Magnetic Fields	EN61000-4-8	100A/m continuous; 1000A/m 1s	A	-

Specifications		
Model		PXD40
<b>Output</b>		
Output Voltage Tolerance	%	± 1
Output Voltage Adjustment	%	Single output only. 3.3V-12V, 48V: ±10, 15V-24V: -10/+20, Dual output none
Switching Frequency	kHz	225 - 275
Line Regulation	%	± 0.2
Load Regulation	%	Single output: ±0.3 Dual output: ±0.5
Cross Regulation	%	Dual output: ±5 (Asymmetrical 25% to 100% load change)
External Load Capacitance	uF	See model selector table
Ripple & Noise (1)	mVp-p	Single output: 3.3-5V outputs: 75, 12-15V outputs: 100, 24V outputs: 150, 48V outputs: 300
Temperature Coefficient	%/°C	± 0.02
Minimum Load	-	No minimum load required
Transient Loading	-	250us recovery time for a 25% load change
Overcurrent Protection (typ)	%	150, hiccup mode
Overvoltage Protection (typ)	V	Zener clamp method. 3.3V: 3.9, 5V: 6.2, 12V: 15, 15V: 20, 24V: 30, 48V: 60
Overtemperature Protection	°C	115
Remote Sense	-	No remote sense
Remote On/Off	-	Positive Logic (Blank): ON: Open or 3-12V, OFF Short or 0-1.2V Negative Logic (-N): ON: Short or 0-1.2V, OFF: Open or 3-12V
<b>Environmental</b>		
Operating Temperature (2)	°C	-40 to +105 - see derating section and instruction manual on website (Confirm case temperatures in end system)
Maximum Case Temperature	°C	105 (Overtemperature Protection 115)
Thermal Impedance	°C/W	No heatsink: 10.8, -HC1: 9.3, -HC2: 7.7, -HC3: 6.2
Storage Temperature	°C	-55 to +125
Humidity (non condensing)	%RH	5 - 95 (Operating & Storage)
Cooling	-	Convection or forced air
Altitude	m	5,000 (operating)
Withstand Voltage (For 1 minute)	Vdc	Input to output 1,600
Isolation Capacitance	pF	1500
Vibration (Operating)	-	MIL-STD-810F
Thermal Shock	-	MIL-STD-810F
<b>Other</b>		
Weight (Typ)	g	34 (no heatsink)
Size (LxWxH)	mm	50.8 x 25.4 x 10.2 (no heatsink)
Size (LxWxH)	Inches	2 x 1 x 0.4 (no heatsink)
Case Material	-	Copper
MTBF - MIL-HDBK-217F, Full Load	Hours	1,245,000
Warranty	yrs	3

**Notes**


See website for detailed specifications, test methods and installation manual

(1): Measured with a 20MHz bandwidth oscilloscope across a 1uF/100V X7R multi-layer ceramic capacitor


(2). The case temperature must be confirmed in end application. The product rating may be affected by airflow direction and physical obstructions near the module.

**Derating Section**

**PXD40-24WS05 - Derating Diagram**




**PXD40-24WS05 - Derating Diagram**



The required power reduction depends on the individual device. The example shows the PXD40-24WS05. The points A to G describe the temperatures at which the power reduction starts. For other models, these points can be taken from the table.

Derating Starting Point	A 20LFM (convection)	B 100LFM	C 200LFM	D 500LFM	E with HS1	F with HS2	G with HS3
PXD40-24WS3P3	53°C	73°C	82°C	86°C	57°C	62°C	65°C
PXD40-24WS05	69°C	83°C	88°C	92°C	74°C	81°C	84°C
PXD40-24WS12	68°C	82°C	88°C	91°C	73°C	80°C	83°C
PXD40-24WS15	71°C	84°C	90°C	93°C	76°C	83°C	87°C
PXD40-24WS24	56°C	78°C	85°C	89°C	60°C	65°C	68°C
PXD40-24WD12	63°C	79°C	86°C	89°C	67°C	74°C	77°C
PXD40-24WD15	64°C	80°C	87°C	90°C	69°C	75°C	78°C
PXD40-24WD24	63°C	79°C	87°C	90°C	67°C	74°C	77°C
PXD40-48WS3P3	55°C	74°C	82°C	87°C	59°C	64°C	67°C
PXD40-48WS05	63°C	79°C	86°C	89°C	67°C	74°C	77°C
PXD40-48WS12	68°C	82°C	88°C	91°C	73°C	80°C	83°C
PXD40-48WS15	73°C	85°C	91°C	94°C	78°C	85°C	89°C
PXD40-48WS24	66°C	81°C	87°C	90°C	71°C	77°C	81°C
PXD40-48WD12	63°C	79°C	86°C	90°C	67°C	74°C	77°C
PXD40-48WD15	63°C	80°C	86°C	90°C	67°C	74°C	77°C
PXD40-48WD24	67°C	82°C	87°C	91°C	72°C	78°C	82°C

## Outline Drawing




## Pinout


PIN	Function	
	Single	Dual
1	+Vin	
2	-Vin	
3	Ctrl	
4	+Vout	
5	-Vout	Com
6	Trim	-Vout

- All dimensions in inch (mm)  
Tolerance:  $x.xx \pm 0.02$  [ $x.x \pm 0.5$ ]  
 $x.xx \pm 0.02$  [ $x.x \pm 0.25$ ]
- Pin dimension tolerance  $\pm 0.004$  [0.10]

## Recommended Pcb Layout




## Recommended Pcb Layout



All dimensions in inch[mm]  
 Pad size(lead free recommended)  
 Through hole 1.2.3.4.5.6:  $\phi 0.051$ [1.30]  
 Top view pad 1.2.3.4.5.6:  $\phi 0.064$ [1.63]  
 Bottom view pad 1.2.3.4.5.6:  $\phi 0.102$ [2.60]


**Heat-Sink Type Options**

**HC1**




SIDE VIEW

**HC2**



SIDE VIEW

**HC3**



SIDE VIEW

1. All dimensions in inch [mm]  
 2. Tolerance :x.xx±0.02 [x.x±0.5]  
 x.xxx±0.010 [x.xx±0.25]



## TDK-Lambda France SAS

Tel: +33 1 60 12 71 65  
france@fr.tdk-lambda.com  
www.emea.lambda.tdk.com/fr



## Italy Sales Office

Tel: +39 02 61 29 38 63  
info.italia@it.tdk-lambda.com  
www.emea.lambda.tdk.com/it



## Netherlands

info@nl.tdk-lambda.com  
www.emea.lambda.tdk.com/nl



## TDK-Lambda Germany GmbH

Tel: +49 7841 666 0  
info@de.tdk-lambda.com  
www.emea.lambda.tdk.com/de



## Austria Sales Office

Tel: +43 2256 655 84  
info@at.tdk-lambda.com  
www.emea.lambda.tdk.com/at



## Switzerland Sales Office

Tel: +41 44 850 53 53  
info@ch.tdk-lambda.com  
www.emea.lambda.tdk.com/ch



## Nordic Sales Office

Tel: +45 8853 8086  
info@dk.tdk-lambda.com  
www.emea.lambda.tdk.com/dk



## TDK-Lambda UK Ltd.

Tel: +44 (0) 12 71 85 66 66  
info@uk.tdk-lambda.com  
www.emea.lambda.tdk.com/uk



## TDK-Lambda Ltd.

Tel: +9 723 902 4333  
info@tdk-lambda.co.il  
www.emea.lambda.tdk.com/il



## C.I.S.

### Commercial Support:

Tel: +7 (495) 665 2627

### Technical Support:

Tel: +7 (812) 658 0463  
info@tdk-lambda.ru  
www.emea.lambda.tdk.com/ru



## TDK-Lambda Americas

Tel: +1 800-LAMBDA-4 or 1-800-526-2324  
powersolutions@us.tdk-lambda.com  
www.us.lambda.tdk.com



## TDK Electronics do Brasil Ltda

Tel: +55 11 3289-9599  
sales.br@tdk-electronics.tdk.com  
www.tdk-electronics.tdk.com/en



## TDK-Lambda Corporation

Tel: +81-3-6778-1113  
www.jp.lambda.tdk.com



## TDK-Lambda (China) Electronics Co. Ltd.

Tel: +86 21 6485-0777  
powersolutions@cn.tdk-lambda.com  
www.lambda.tdk.com.cn



## TDK-Lambda Singapore Pte Ltd.

Tel: +65 6251 7211  
tts.mkt@sg.tdk-lambda.com  
www.sg.lambda.tdk.com



## TDK India Private Limited, Power Supply Division

Tel: +91 80 4039-0660  
mathew.philip@in.tdk-lambda.com  
www.sg.lambda.tdk.com

