



Ref. Certif. No.

US-TUVR-5296-A3

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

SYSTEME CEI D' ACCEPTATION MUTUELLE DE CERTIFICATS D'ESSAIS DES EQUIPEMENTS ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product
Produit

Switch Mode Power Supply

Name and address of the applicant
Nom et adresse du demandeur

TDK-Lambda Americas Inc.
401 Mile of Cars Way, Suite 325
National City, CA 91950 US

Name and address of the manufacturer
Nom et adresse du fabricant

same as applicant

Name and address of the factory
Nom et adresse de l'usine

Power-Win Technology Corporation
B1F-2, No. 75, 1 Hsin Tai 5th Road,
SHI CHI, NEW TAIPEI CITY
TAIWAN - R.O.C.

*Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} page*

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Additional Information, see page 2

Trademark (if any)
Marque de fabrique (si elle existe)

TDK-Lambda

Model / Type Ref.
Ref. De Type

Additional Information, see page 2

Additional information (if necessary, may also be reported on page 2)
Les informations complémentaires (si nécessaire, peuvent être indiqués sur la 2^{ème} page)

Re-issuance of Certificate US-TUVR-5296 due to 3rd modification (change of applicant address). See associated test report for details (TMP)

A sample of the product was tested and found to be in conformity with IEC
Un échantillon de ce produit a été essayé et a été considéré conforme à la CEI


IEC 60601-1

3rd Edition (2005)

As shown in the Test Report Ref. No. which forms part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de référence qui constitue partie de ce Certificat

30992615.005

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



Date: November 17, 2014

Page 1 of 2

Signature:

Martin Glagla
Martin Glagla



Ref. Certif. No.

US-TUVR-5296-A3

Additional Information:

Ratings and principal characteristics:

AC 100-240V, 50-60Hz; 2.5A or
DC 120-180V, 2.5A
Class I


Output Ratings DC:

- 1) 12V/8.3A, 100W max. convection; 12V/12.5A, 150W max. w/15CFM forced air;
- 2) 15V/6.7A, 100W max. convection; 15V/10.0A, 150W max. w/15CFM forced air;
- 3) 24V/4.2A, 100W max. convection; 24V/6.3A, 150W max. w/15CFM forced air;
- 4) 36V/2.8A, 100W max. convection; 36V/4.2A, 150W max. w/15CFM forced air;
- 5) 48V/2.1A, 100W max. convection; 48V/3.1A, 150W max. w/15CFM forced air

Model / Type Ref.:

- 1) CSS150-12, 2) CSS150-15, 3) CSS150-24, 4) CSS150-36, 5) CSS150-48

This CB Test Certificate is issued by the National Certification body TÜV Rheinland of North America, Inc.
Ce Certificat d'essai OC est établi par l'Organisme National de Certification TÜV Rheinland of North America, Inc.



November 13, 2014

Page 2 of 2

Date:

Signature:

Martin Glägl
Martin Glägl