



Test Report issued under
the responsibility of:



TEST REPORT
IEC 61010-1
Safety requirements for electrical equipment for measurement, control, and
laboratory use
Part 1: General requirements

Report Reference No : E331788-A16-CB-2
Date of issue : 2015-10-20
Total number of pages : 133

CB Testing Laboratory : UL International Demko A/S
Address : Borupvang 5A, 2750 Ballerup, Denmark

Applicant's name : TDK-LAMBDA UK LTD
KINGSLEY AVE
Address : ILFRACOMBE
DEVON
EX34 8ES UNITED KINGDOM

Test specification:

Standard : IEC 61010-1:2010, 3rd Edition
Test procedure : CB Scheme
Non-standard test method : N/A

Test Report Form No. : IEC61010_1H
Test Report Form originator : VDE Testing and Certification Institute
Master TRF : 2011-11

Copyright © 2011 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.


This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.




If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description	Switch Mode Power Supply
Trade Mark	TDK-Lambda Ltd
	
Manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Model/Type reference	EFE300M Series (EFE300Mxy-a-b-cdef-ghijk) or Y5J008# or Y5J006# (where # can be any letter) (see model differences for details of models and nomenclature)
Ratings	100-240Vac nom, 4.9A rms max, 45-440Hz (See model differences for details of ratings)

Testing procedure and testing location:	
<input type="checkbox"/> CB Testing Laboratory	Testing location / address
<input type="checkbox"/> Associated CB Test Laboratory	Testing location / address
	Tested by (name + signature)
	Approved by (name + signature).....
<input type="checkbox"/> Testing Procedure: TMP/CTF Stage 1	Testing location / address
	Tested by (name + signature)
	Approved by (name + signature).....
<input type="checkbox"/> Testing Procedure: WMT/CTF Stage 2	Testing location / address
	Tested by (name + signature)
	Witnessed by (name + signature) ..
	Approved by (name + signature).....
<input checked="" type="checkbox"/> Testing Procedure: SMT/CTF Stage 3 or 4	Testing location / address: TDK-Lambda Ltd, Kingsley Avenue, Ilfracombe, Devon, EX348ES. United Kingdom.
	Tested by (name + signature): N. S. Marsh 
	Approved by (name + signature).....: K. P. Tizzard 
	Supervised by (name + signature) .: Bartlomiej Zmijewski 
<input type="checkbox"/> Testing Procedure: RMT	Testing location / address
	Tested by (name + signature)
	Approved by (name + signature).....
	Supervised by (name + signature) .:

List of Attachments
National Differences (15 pages)
Enclosures (146 pages)
Summary Of Testing
Unless otherwise indicated, all tests were conducted at TDK-Lambda Ltd, Kingsley Avenue, Ilfracombe, Devon, EX348ES. United Kingdom..

Tests performed (name of test and test clause)	Testing location / Comments
Single Fault Conditions Tests (4.4) Component Abnormal (4.4.1) Dielectric Strength Test (6.8) Temperature Test (10.1-10.4)	
Summary of Compliance with National Differences: Countries outside the CB Scheme membership may also accept this report. List of countries addressed: AT, BE, CA, CH, CZ, DE, DK, FI, FR, GB, IL, IT, JP, NO, SE, SI, SK, US The product fulfills the requirements of: UL 61010-1 3rd Ed. CAN/CSA 22.2 No. 61010-1-12 3rd Ed. EN 61010-1:2010.	

Copy of Marking Plate

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.



Test item particulars :	
Type of item tested	Laboratory
Description of equipment function	Switch Mode Power Supply for building in.
Connections to mains supply	None
Overvoltage category	II
Pollution degree	2
Means of Protection	Class I (PE connected)
Environmental conditions	Normal
For use in wet locations	No
Equipment mobility	Built-in
Operating conditions	continuous
Overall size of the equipment: (W X D X H) (mm) :	164mm x 85mm x 41mm maximum
Mass of the equipment (kg)	1kg maximum
Marked degree of protection to IEC 60529	None
Possible test case verdicts:	
- test case does not apply to the test object	N / A
- test object does meet the requirement	P(Pass)
- test object does not meet the requirement	F(Fail)
Testing:	
Date(s) of receipt of test item	2013-06-25, 2014-12-03, 2014-12-10, 2015-01-05
Date(s) of Performance of tests	2013-07-05 to 2013-07-08, 2014-12-09 to 2015-01-07
General remarks:	
"(see Enclosure #)" refers to additional information appended to the report.	
"(see Form A.xx)" refers to a table appended to the report.	
Bottom lines for measurement tables Form A.xx are optional if used as record.	
Throughout this report a point is used as the decimal separator.	
Manufacturer's Declaration per Sub Clause 4.2.5 of IEC60068-2-21:	
The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided	
When differences exist, they shall be identified in the General Product Information section.	
Name and address of Factory(ies):	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM PANYU TRIO MICROTRONIC CO LTD

SHIJI INDUSTRIAL ESTATE
DONGYONG
NANSHA
GUANGZHOU GUANGDONG
CHINA

GENERAL PRODUCT INFORMATION:

Report Summary

All applicable tests according to the referenced standard(s) have been carried out.

Product Description

EFE300M series. Switch mode power supplies for building into end equipment.

Model Differences

Nominal Input Voltage Range	100 - 240V AC
Maximum Input Voltage Range	90** - 264V AC
Input Frequency	45-440* Hz maximum
Maximum Input Current	4.9A rms

** Channel 1 output is linearly derated from 90Vac to 85Vac, 4W per volt to 280W.

All ratings apply for ambient temperatures up to 50°C. From 50 to 70°C the output power is derated at 2.5% per deg C.

EFE300M or -EFE300M models as described below:

(may be prefixed by NS - # / where # may be any characters indicating non safety related model differences)
Products may additionally be marked with U5x or Y5x where x can be any characters indicating non-safety related model differences.

Unit Configuration Code: EFE300Mxy-a-b-cdef-ghijk
where:

x= Nothing or J for Japanese models (may have non-safety differences).
Y= Blank for Y2 capacitors from output to earth, P for Y1 capacitors from output to earth.
a= Channel 1 output Voltage: see Ch1 in the outputs table below, adjustment range column.
b= Standby voltage: see standby voltage table below or 0 for omitted
c= HN for Open frame, no fan, with 12V / 1A fan supply. HU for U chassis, no fan, with 12V / 1A fan supply. HC for Cover + chassis, no fan, with 12V / 1A fan supply. EC for Cover + chassis, end fan (temp controlled). NN for Open frame, no fan, no fan supply. NU for U chassis, no fan, no fan supply. NC for Cover + chassis, no fan, no fan supply. CN for Open frame, no fan, with 12V / 0.25A fan supply. CU for U chassis, no fan, with 12V / 0.25A fan supply. CC for Cover + chassis, no fan, with 12V / 0.25A fan supply.
d= M for molex input connector or equivalent, J for JST connector or equivalent.
e= D for dual fused input or L for single fuse in the live line.
f= S for standard Leakage, L for low Leakage, R for reduced Leakage, T for tiny Leakage. *
g= Y for Oring FET included or N for nothing.
h= E for enable, T for inhibit, N for no inhibit, no enable.
i= Nothing for horizontal output connector, -V for vertical output connector, -S for screw terminal
j= Nothing for standard channel 1 output voltage, -xD or -xPD where D is for units with programmed negative load regulation, PD is for units with programmed positive load regulation, x is the voltage of the

regulation in 100mVolts and is within the Output Adjustment range (example, 7D = 0.7V of negative load regulation, 24PD = 2.4V of positive load regulation).

k= Nothing or -x where x is three numbers from 0 to 9 which denotes various output voltage/current settings within the specified ranges of each output for a particular unit or blank for standard output settings. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP)

* At 440Hz, leakage current is > 3.5mA and therefore must be assessed in the end use application. L < 300uA leakage, R < 150uA leakage and T < 75uA leakage.

Output parameters:

O/P Channel	Vout nom.	Range (V)	O/P Current (A)	Max O/P Power (W)
CH1	12	11.4 - 13.2*	25	300 (400**)
	24	22.8 - 26.4*	12.5	300 (400**)
	28	27 - 32*	10.72	300 (400**)
	40	36 - 42*	7.5	300 (350***)
	48	47 - 50*	6.25	300 (350***)
	50	50.1 - 54* 6.0		300 (350***)
Standby	5	Fixed	2	10
	12	12-13.5*	1	13.5
Fan output	12	Fixed	0.25	3
	12	Fixed	1	12

* Can be adjusted from nominal at the factory only.

** Peak power of 400W for 10 seconds maximum, maximum rms power of 300W:

*** Peak power of 350W for 10 seconds maximum, in any 1 minute cycle, maximum rms power of 300W:

where T1 = peak power time on
and T2 = reduced power time on

Maximum continuous power output 300W (excluding fan output)

Output Limitations

All standard outputs are SELV up to and including 48V nominal. Voltages above 48V nominal are non SELV and must not be accessible to an end operator..

All outputs have basic spacings to earth, and due consideration must be given to this in the end product design, except for Y50029# (60950-1 approved model) which has functional spacings to earth.

Non Standard models.

Model: Y5J008# (where # can be any letter) or EFE300MJ-12.1-5-008 or EFE300MJ-12.1-5-008-SGP

Maximum outputs: 12.1V, 21.49A, plus 5V, 2A standby.

Maximum ambient: As standard model.

Orientations: As standard model.

Comments: Fan speed is controlled at 6600rpm up to and between 45 to 50 degrees C ambient after which the fan resumes its normal nominal voltage rating. Can be fitted with or without fan guard. Model may also include a without fan and open frame type.

Model: Y5J006# (where # can be any letter) or EFE300MJ-12-5-006.

Maximum outputs: 11.4V to 13.2V*, 25A, (300W max) plus 5V, 2A standby.

Maximum ambient: As standard model.

Orientations: As standard model.

Comments: Longer version than standard model to accommodate additional reservoir capacitor for a greater hold up time.

Additional Information

This report is a reissue of CBTR Ref. No: E331788-A16-CB1 dated 2013-07-25 and CB certificate DK-33970-UL dated 2013-07-25. Based on the previously conducted testing, limited testing for this report and the review of product technical documentation including photos, schematics, wiring diagrams and similar, it has been determined that the product complies with the standard.

The original report has been modified for the following:

1) Addition/deletion to the critical components list and new certificates.

2) Added two new transformer part numbers and drawings.

TX1: 230130 is identical to the other TX1 transformers used for standard models but includes an additional comment for Sony models Y5J008# and Y5J0015#.

TX2: 230129 is identical to the other TX2 transformers used for standard models but includes an additional comment for Sony models Y5J008# and Y5J015#.

3) Alternate fan.

4) Alternative fuse testing (not mains input fuse)

5) CBTL updated from UK to UL international Demko A/S.

Technical Considerations

- Equipment classification: Commercial, Professional
- Equipment class: Class I
- Equipment type: For building in
- The product was submitted and tested for use at the maximum recommended ambient temperature (T_{mra}) of: 50°C maximum load, 70°C reduced load.

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- This component has been judged on the basis of the creepage and clearances required in the indicated Standards, which would cover the component itself if submitted for Listing: UL 61010-1 3rd Ed., CAN/CSA 22.2 No. 61010-1-12 3rd Ed., IEC 61010-1:2010 3rd Ed., EN 61010-1:2010.
- The end-product shall consider that: The enclosure does not serve as a fire/electrical/mechanical enclosure
- The need for the following shall be considered in the end-product: Bonding to protective earthing terminal (Class I construction)
- The output connectors are: Not investigated for field wiring
- Creepage and clearance distances were based on a maximum working voltage of: Primary to earth dead metal: 668V_{peak}, 348V_{rms}., Primary to secondary: 880V_{peak}, 408V_{rms}.
- Insulation between primary circuits and accessible dead metal complies with the requirements for : Basic insulation
- Insulation between primary and secondary circuits complies with the requirements for: Reinforced insulation
- The following tests shall be performed in the end-product evaluation: Dielectric Strength test in accordance with the handbook., Temperature test for customer air models.,

- The unit is considered acceptable for use at on a max branch circuit of: 20A
- The unit is considered acceptable for use in a max ambient of: 50°C maximum load, 70°C reduced load.
- End-product temperature tests for power supplies shall consider that the following transformers employ the indicated insulation system: Transformer Tx1, Class F (155°C)., Transformer Tx2, Class F (155°C).
- End-product dielectric strength tests shall be based on the maximum working voltage of: Primary to earth dead metal: 668Vpeak, 348Vrms., Primary to secondary: 880Vpeak, 408Vrms.
- The leakage current tests have been provided for information only. This test must be considered in the end product application and must be repeated for frequencies above 63Hz. --
- This product has been assessed for a maximum altitude of 5000m --
- The risk associated with clause 5.4.5 shall be assessed in the end product. --
- Multi-layer PWBs accepted under CBTR Ref. No: E349607-A23 dated 2014-07-31 and letter report in Enclosure 8-03 of this report. --