



Ref. Certif. No.

US-TUVR-9461

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEMESYSTEME CEI D' ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product
Produit

Programmable Power Supply

Name and address of the applicant
Nom et adresse du demandeurTDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
Karmiel 2161401 ISRAELName and address of the manufacturer
Nom et adresse du fabricant

same as applicant

Name and address of the factory
Nom et adresse de l'usine

same as applicant

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} pageRatings and principal characteristics
Valeurs nominales et caractéristiques principales

Additional Information, see page 2

Trademark (if any)
Marque de fabrique (si elle existe)

TDK-Lambda

Model / Type Ref.
Ref. De Type

Additional Information, see page 2

Additional information (if necessary, may also be
reported on page 2)
Les informations complémentaires (si nécessaire,
peuvent être indiqués sur la 2^{ème} page)Complies with requirements as well as group and national differences
where applicable for DK, IT, SE, and US as well as EU Group
Differences and EU Special National Conditions.
Replaces Certificate US-TUVR-7687.A sample of the product was tested and found
to be in conformity with IEC
Un échantillon de ce produit a été essayé et a été
considéré conforme à la CEI

IEC 60950-1+Amd1+Amd2

2nd Edition (2005)

As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

30581080.014

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**

Date: February 12, 2016

Page 1 of 2

Signature:

Martin Glagla



Ref. Certif. No.

US-TUVR-9461

Additional Information:

Model / Type Ref.:

GEN3300W Series, PU3300W Series, Models:
GENwww-xxx-y-z-u-CO-o, PUwww-xxx-y-z-u-CO-o
(www = 008-600;
xxx = 005-400;
y = LAN, MD, IEEE, IEMD, IS420, IS510, USB, blank;
z = 1P230, 3P208, 3P400;
u = U, blank;
CO = -CO, blank;
o = -1683, -1690, -1704, -1706, -171X (X=0-9), -1733, -1737, -174X, -174X (X=4-9), blank)

Ratings and principal characteristics:

- 1) 1-Phase units: AC 190-240V; 50/60Hz, 22A
 - 2) 3-Phase units: AC 190-240V; 3wire+PE, 50/60Hz, 12.5A or
AC 380-415V; 3wire+PE, 50/60Hz, 6.5A
- Class I
Output Ratings: DC 0-8V/400A max. to DC 0-600V/5.5A max; 3300W max.

This CB Test Certificate is issued by the National Certification body TUV Rheinland of North America, Inc.
Ce Certificat d'essai OC est établi par l'Organisme National de Certification TUV Rheinland of North America, Inc.



Date: February 12, 2016

Page 2 of 2

Signature:


Martin Glagla