




Ref. Certif. No.

**DK-74040-UL**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME**

**CB TEST CERTIFICATE**

Product	Switch mode power supply
Name and address of the applicant	TDK LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE NORTH DEVON EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE NORTH DEVON EX34 8ES UNITED KINGDOM
Name and address of the factory	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM
Note: <i>When more than one factory, please report on page 2</i>	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark (if any)	TDK-Lambda 
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	QM5 and QS5, QM7 or QS7, QM8 switch mode power supplies (followed by alphanumeric characters - see Test Report for details of models and nomenclature)
Additional information (if necessary may also be reported on page 2)	National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60601-1(ed.2), IEC 60601-1(ed.2);am1, IEC 60601-1(ed.2);am2
As shown in the Test Report Ref. No. which forms part of this Certificate	E349607-A43-CB-2 issued on 2018-06-20

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 8F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2018-06-21

Signature:

Jan-Erik Storgaard

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)



Ref. Certif. No.

**DK-74040-UL**

**Factories:**

PANYU TRIO MICROTRONICS CO LTD  
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG  
CHINA

**Ratings:**

QM5 or QS5 (700W): 100-240Vac nom, 47-63Hz, 11A rms max  
QM5 or QS5 (1200W): 200-240Vac nom, 47-63Hz, 9A rms max  
QM5 or QS5 (700W): 144-270Vdc nom, 7Adc max  
QM5 or QS5 (1200W): 239-270Vdc nom, 7Adc max  
QM7 or QS7 (1200W): 100-240Vac nom, 47-63Hz, 19A rms max  
QM7 or QS7 (1500W): 166.7-240Vac, 47-63Hz, 14A rms max  
QM8 (1200W): 100-240Vac nom, 47-63Hz, 19A rms max  
QM8 (1500W): 166.7-240Vac nom, 47-63Hz, 14A rms max

**Additional information (if necessary)**



- UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2018-06-21

Signature:

Jan-Erik Storgaard