

TDK-Lambda UK Limited
Kingsley Avenue, Ilfracombe
Devon, EX34 8ES, United Kingdom
Tel: +44 (0) 1271 856600
Fax: +44 (0) 1271 864894
www.emea.lambda.tdk.com/uk

EU DECLARATION OF CONFORMITY



EFE400 Series

We, TDK Lambda UK Limited, of Kingsley Avenue, Ilfracombe, Devon, EX34 8ES declare under our sole responsibility that the TDK-Lambda power supplies, as detailed on the attached products covered sheets, comply with the provisions of the following European Directives and are eligible to bear the CE mark:

Low Voltage	Directive 2014/35/EU
EMC	Directive 2014/30/EU
RoHS	Directive 2011/65/EU (as amended by 2015/863)

Assurance of conformance of the described product with the provisions of the stated EC Directive is given through compliance to the following standards:

Electrical Safety (LVD)	EN 62368-1:2014/AC:2015
Electromagnetic Compatibility (EMC)	EN 61000-6-3:2007 + A1:2011 EN 61000-6-2:2005 EN 61204-3:2000 EN 55024:2010 EN 55032:2015
Restriction of Hazardous Substances (RoHS)	EN 63000:2018

Our representative in the EU is TDK-Lambda Germany GmbH, located at Karl-Bold-Str. 40, 77855 Achern, Germany.

Note: The EMC performance of a component power supply will be affected by the final installation, compliance to the stated EMC standards and conformance to the EMC Directive must be confirmed after installation by the final equipment manufacturer. For guidance with respect to test conditions please visit our website at https://emea.lambda.tdk.com/EMC_Guidance or contact your local TDK-Lambda sales office.

TDK-Lambda UK Limited
Kingsley Avenue, Ilfracombe
Devon, EX34 8ES, United Kingdom
Tel: +44 (0) 1271 856600
Fax: +44 (0) 1271 864894
www.emea.lambda.tdk.com/uk

UK DECLARATION OF CONFORMITY



EFE400 Series

We, TDK Lambda UK Limited, of Kingsley Avenue, Ilfracombe, Devon, EX34 8ES declare under our sole responsibility that the TDK-Lambda power supplies, as detailed on the attached products covered sheets, comply with the provisions of the following European Directives and are eligible to bear the UKCA mark:

Electrical Equipment (Safety) Regulations 2016

Electromagnetic Compatibility Regulations 2016

Restriction of the Use of Certain Hazardous Substances in Electrical & Electronic Equipment Regulations 2012

Assurance of conformance of the described product with the provisions of the stated UK Regulation is given through compliance to the following standards:

Electrical Safety	EN 62368-1:2014/AC:2015
Electromagnetic Compatibility (EMC)	EN 61000-6-3:2007 + A1:2011 EN 61000-6-2:2005 EN 61204-3:2000 EN 55024:2010 EN 55032:2015
Restriction of Hazardous Substances (RoHS)	EN 63000:2018

Note: The EMC performance of a component power supply will be affected by the final installation, compliance to the stated EMC standards and conformance to the EMC Regulation must be confirmed after installation by the final equipment manufacturer. For guidance with respect to test conditions please visit our website https://emea.lambda.tdk.com/EMC_Guidance or contact your local TDK-Lambda sales office.

EFE400 Series Products Covered

EFE400 or EFE-400 models as described below:

Units may be additionally marked with a Product Code: U4x or Y4x where x may be any number of characters.

Unit Configuration Code (Description :) may be prefixed by NS # (where # may be any number of characters indicating non- safety related model differences).

Unit Configuration Code:

EFE400x-a-bcde-f-g-hij

Where:

x = Nothing or J for Japanese models (may have non-safety differences)

a = Channel 1 Output Voltage: any voltage within the Adjustment Range for the Vout (nom) from the Output Table below, e.g. 12.8 for 12.8V output (12Vout nom), 24.6 for 24.6V output (24Vout nom).

b = CN for Open Frame with fan output, CU for U chassis with fan output, CC for U chassis and cover with fan output, EC for U chassis and cover with fan (temperature controlled).

c = M for molex input connector or equivalent, J for JST connector or equivalent.

d = D for dual fused input, FL for single fuse input in the Live Line.

e = S for Standard Leakage, L for Low Leakage, R for Reduced Leakage, T for Tiny Leakage.*

f = Nothing for horizontal output connector, V for vertical output connector.

g = Nothing for standard channel 1 output voltage, xD or xPD where D is for units with programmed negative load regulation, PD is for units with programmed positive load regulation, x is the voltage of the regulation in 100mVolts and is within the Output Adjustment range (example, 7D = 0.7V of negative load regulation, 24PD = 2.4V of positive load regulation).

hij = Three numbers from 0 to 9 which denotes various output voltage/current settings within the specified ranges of each output for a particular unit or blank for standard output settings. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP).

Output Parameters

Standard models:

Output Channel	Vout Nom.	Adjustment Range (V)	Output Current (A)	Maximum Power (W)
Channel 1	12	11.4 - 13.2*	33.33	400 (530**)
	24	22.8 - 26.4*	16.67	400 (530**)
Fan output (optional)	12	Fixed	0.25	3

Variations and limitations of use:

1. Maximum ambient 70°C (de-rating output power 2.5% per °C above 50°C).
2. * Can be adjusted at the factory only.
3. Maximum continuous power output 400W (excluding fan output).
4. ** Peak power for 10 seconds maximum, maximum rms power of 400Wrms.

EFE400R or EFE-400R models as described below:

Units may be additionally marked with a Product Code: U4x or Y4x where x may be any number of characters.

Unit Configuration Code (Description :) may be prefixed by NS # (where # may be any number of characters indicating non- safety related model differences).

Unit Configuration Code:

EFE400Rx-a-bcde-km-f-g-hij

Where:

x = Nothing or J for Japanese models (may have non-safety differences)

a = Channel 1 Output Voltage: any voltage within the Adjustment Range for the Vout (nom) from the Output Table below.

b = CN for Open Frame with fan output, CU for U chassis with fan output, CC for U chassis and cover with fan output, EC for U chassis and cover with fan (temperature controlled), NN for open frame with no fan output.

c = M for molex input connector or equivalent, J for JST connector or equivalent.

d = D for dual fused input, FL for single fuse input in the Live Line.

e = S for Standard Leakage, L for Low Leakage, R for Reduced Leakage, T for Tiny Leakage.*

f = Nothing for horizontal output connector, V for vertical output connector.

g = Nothing for standard channel 1 output voltage, xD or xPD where D is for units with programmed negative load regulation, PD is for units with programmed positive load regulation, x is the voltage of the regulation in 100mVolts and is within the Output Adjustment range (example, 7D = 0.7V of negative load regulation, 24PD = 2.4V of positive load regulation).

hij = Three numbers from 0 to 9 which denotes various output voltage/current settings within the specified ranges of each output for a particular unit or blank for standard output settings. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP).

k = Y for or-ing device or N for none fitted.

m = E for enable or T for inhibit.

Output Channel	Vout Nom.	Adjustment Range (V)	Max Output Current (A)	Maximum Power (W)
Channel 1	48	47-50*	8.5	400 (470**)
Fan output (optional)	12	Fixed	0.25	3

Variations and limitations of use:

1. Maximum ambient 70°C (de-rating output power 2.5% per °C above 50°C).
2. * Can be adjusted at the factory only.
3. Maximum continuous power output 400W (excluding fan output).
4. ** Peak power for 10 seconds maximum, maximum rms power of 400Wrms.

EFE400 Series Signature Page

Name of Authorized Signatory	Christopher Haas
Signature of Authorized Signatory	
Position of Authorized Signatory	Head of Quality & Compliance Europe
Date	23 September 2021
Date when this CE declaration first issued	25 February 2009
Date when this UKCA declaration first issued	6 April 2021
Place where signed	Achern, Germany

This declaration is signed for and on behalf of TDK-Lambda