



## 3 x 5" 150W AC-DC Medical Power Supplies

Features	Benefits
• No Load Power <0.5W	• Energy Saving
• Low Profile, Industry Standard Footprint	• Fits 1U Applications
• Dual input fuses	• Simplifies System Design, Reduces Cost




Specification		
Model	CSS150	
Input Voltage range	V	90 - 264VAC (47 - 400Hz)(1) or 120 - 180VDC
Inrush Current	A	<60A maximum at 264VAC input, 25°C ambient cold start
Input Current (115/230VAC)	A	1.7 / 0.85
Power Factor Correction	-	Meets EN61000-3-2, >0.9
Leakage Current	µA	<250µA 264VAC 63Hz
Hold Up Time (Typ)	ms	16ms at 115VAC input
Temperature Coefficient	-	±0.05%/°C
Voltage Accuracy	%	±1%
Minimum Load	A	None
Total Regulation	%	±3%
Ripple & Noise	%	2% peak to peak
Overcurrent Protection	-	110 - 150%
Overvoltage Protection	V	110 - 150% of nominal (Cycle input power to reset)
Remote On/Off	-	Unit on: Floating or low <1.2V, Unit off: Apply 5V with respect to 0V
Efficiency	%	89% typical
No load power	W	<0.5W
Operating Temperature	°C	0 to +70°C derate linearly to 50% load from 50 to 70°C
Storage Temperature	°C	-20°C to +85°C
Humidity (non condensing)	-	20 - 95% RH
Cooling	-	Convection or forced air (2.5m/s)
Withstand Voltage	-	Input to Ground 1.5kVAC, 3kVAC (2 x MOOPs 3rd Edition), Output to Ground 500VDC for 1 min.
Isolation Resistance	Ω	>100M Ω at 25°C & 70%RH, Output to Ground 500VDC
Vibration (non operating)	-	19.6m/s <sup>2</sup> (10~55Hz:2G Constant, X,Y,Z 60min each.)
Shock	G	< 196.1 m/s <sup>2</sup> (2G)
Safety Agency Approvals	-	UL60601-1, EN60601-1, IEC60601-1, UL60950-1, EN60950-1, CE Mark
Conducted & Radiated EMI	-	EN55011-B, FCC Class B
Immunity	-	EN60601-1-2
MTBF	-	180,000 (MIL-217F-HDBK)
Weight (Typ)	g	340g
Size (WxLxH)	mm	127 x 76.2 x 33 (including underside components)
Warranty	yrs	2

(1) Derate linearly to 90W convection rating from 90 to 100VAC input

## Model Selector

Model	Output Voltage (V)	Voltage Adjust (V)	Maximum Current Convection (A)	Maximum Power Convection (W)	Maximum Current Forced Air	Maximum Power Forced Air
CSS150-12	12V	11.64 - 12.36V	8.3A	100W	12.5A	150W
CSS150-15	15V	14.55 - 15.45V	6.7A	100W	10A	150W
CSS150-24	24V	23.28 - 24.72V	4.2A	100W	6.3A	150W
CSS150-36	36V	34.92 - 37.08V	2.8A	100W	4.2A	150W
CSS150-48	48V	46.60 - 49.44V	2.1A	100W	3.1A	150W

## Outline Drawing CSS150 Series





## TDK-Lambda France SAS

ZAC des Delaches  
CS 41077  
9 rue Thuillere  
91978 Villebon Courtaboeuf  
France  
Tel: +33 1 60 12 71 65  
Fax: +33 1 60 12 71 66  
france@tdk-lambda.com  
www.fr.tdk-lambda.com



## Italy Sales Office

Via dei Lavoratori 128/130  
20092 Cinisello Balsamo (MI)  
Italy  
Tel: +39 02 61 29 38 63  
Fax: +39 02 61 29 09 00  
info.italia@it.tdk-lambda.com  
www.it.tdk-lambda.com



## Netherlands

info@tdk-lambda.nl  
www.tdk-lambda.nl



## TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40  
77855 Achern  
Germany  
Tel: +49 7841 666 0  
Fax: +49 7841 5000  
info.germany@de.tdk-lambda.com  
www.de.tdk-lambda.com



## Austria Sales Office

Aredstrasse 22  
2544 Leobersdorf  
Austria  
Tel: +43 2256 655 84  
Fax: +43 2256 645 12  
info.germany@de.tdk-lambda.com  
www.de.tdk-lambda.com



## Scandinavia Sales Office

Valdemarsgade 7  
4100 Ringsted  
Denmark  
Tel: +45 24 63 95 65  
Fax: +45 69 80 44 99  
info@de.tdk-lambda.com  
www.emea.tdk-lambda.com



## Switzerland Sales Office

Bahnhofstrasse 50  
8305 Dietlikon  
Switzerland  
Tel: +41 44 850 53 53  
Fax: +41 44 850 53 50  
info@de.tdk-lambda.com  
www.de.tdk-lambda.com



## TDK-Lambda UK Ltd.

Kingsley Avenue  
Ilfracombe  
Devon EX34 8ES  
United Kingdom  
Tel: +44 (0) 12 71 85 66 66  
Fax: +44 (0) 12 71 86 48 94  
powersolutions@uk.tdk-lambda.com  
www.uk.tdk-lambda.com



## TDK-Lambda Ltd.

Kibbutz  
Givat Hashlosha 48800  
Israel  
Tel: +9 723 902 4333  
Fax: +9 723 902 4777  
info@tdk-lambda.co.il  
www.tdk-lambda.co.il



## C.I.S.

**Commercial Support:**  
Tel: +7 (495) 665 2627  
**Technical Support:**  
Tel: +7 (812) 658 0463  
info@tdk-lambda.ru  
www.tdk-lambda.ru

## Local Distribution

