

TDK-Lambda UK Limited
Kingsley Avenue, Ilfracombe
Devon, EX34 8ES, United Kingdom
Tel: +44 (0) 1271 856600
Fax: +44 (0) 1271 864894
www.uk.tdk-lambda.com

EU DECLARATION OF CONFORMITY

XMS Series

We, TDK-Lambda UK Limited, of Kingsley Avenue, Ilfracombe, Devon, EX34 8ES declare under our sole responsibility that the TDK-Lambda XMS series of power supplies, as detailed on the attached products covered sheets, complies with the provisions of the following European Directives and is eligible to bear the CE mark:


Low Voltage Directive	2014/35/EU
EMC Directive	2014/30/EU
RoHS 2 Directive	2011/65/EU

Assurance of conformance of the described product with the provisions of the stated EC Directive is given through compliance to the following standards:

Electrical Safety (LVD)	EN60950-1:2006 + A2:2013
Electromagnetic Compatibility (EMC)	EN61000-6-3:2007 + A1:2011 EN61000-6-2:2005 EN55011:2009 + A1:2010 EN55024:2010 EN55032:2015

Our European Representative in the EU is TDK-Lambda UK Limited, located at Kingsley Avenue, Ilfracombe, Devon, EX34 8ES, UK.

Note: The EMC performance of a component power supply will be affected by the final installation, compliance to the stated EMC standards and conformance to the EMC Directive must be confirmed after installation by the final equipment manufacturer.
For guidance with respect to test conditions please visit our website at <https://emea.tdk-lambda.com/EMC> Guidance or contact your local TDK-Lambda sales office.

Name of Authorized Signatory	Martin Southam
Signature of Authorized Signatory	
Position of Authorized Signatory	Marketing Director, TDK-Lambda EMEA
Date	13 th July 2018
Date when first CE marked	02 November 2015
Place where signed	Ilfracombe, Devon, England

XMS PRODUCTS COVERED

Model Differences –

XMS350 or XMS500 series (may also be marked as XMS-350 or XMS-500) as described below:

Units may be marked with a Product Code: Xy where y may be any number of characters.

Unit Configuration Code (Description): may be prefixed with NS # followed by / or - (where # may be any number of characters indicating non-safety related model differences).

Unit Configuration (Description)

XMSxy-a-bc-defghijklm

where:

- x = 350 for 350W model
500 for 500W model
500P for 576W peak power models (36V, 40V and 48V output models only)
- y = Blank for Class I
D for Class II
- a = Channel 1 Output Voltage (see Ch1 in the table below, adjustment range column).
- b = Standby Output Voltage: see standby voltage in table below
N for no supply
5 for 5 volt
12 for 12 volt
- c = Standby Output Current†:
C for 0.5A
M for 1.0A
H for 2.0A
N for no supply or 0 amps output
- d = Fan Supply†:
N for no fan supply (customer cooling)
N1 for 24V fan supply (customer cooling)
N2 for 12V variable supply
N3 for 12V fixed supply
KF for non-standard top fan
TF for top-fan
- e = U for non-standard U chassis
P for perforated frame
N for Open Frame
C for custom chassis/covers for non-standard models
S for standard U chassis
B for standard U chassis with perforated cover
- f = Touch (Enclosure) current:
B for <100uA
T for <75uA
- g = Earth leakage current:
D for Class II (no Earth)
L for <300uA
R for <150uA
T for <100uA

- h = E or In for inhibit
T or En for enable
- i = A for AC OK option
N for no AC OK option
- j = Blank for dual fuses fitted
FL for single fuse fitted in the Live line

klm = Blank for standard output settings

May be three numbers from 0 to 9 (preceded by -) which denotes various output voltage/current settings within the specified ranges of each output for a particular unit. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP)

Input Parameters

Nominal input voltage 100 - 240 Vac
 Input voltage range 90 - 264 Vac
 Input frequency range 47 - 63 Hz
 Maximum input current 7A (5.3A*) rms
 * Input for 350W models.

All ratings apply for ambient temperatures up to 50°C.

Output Parameters

†Output ratings are in accordance with the following table:

Standard models:

Output Channel	Voltage Designation	Vout nom.(V)	Adjustment Range (V)	Output Current (A)	Output Power (W)
CH1 (500W)	12	12	11.6 - 13.2	41.6	500
	24	24	23.8 - 25.2	20.8	500
	36	36	35.4 - 37.8	13.8(16*)	500(576*)
	40	40	38 - 42	12.5(15.16*)	500(576*)
	48	48	47-50	10.4(12*)	500(576*)
CH1 (350W)	24	24	23.8 - 25.2	14.6	350
Standby Option	5	5	5 - 5.5	0.5	2.75
	5	5	5 - 5.5	2.0	11.0
	12	12	12-13.2	1	13.2
	N	10	5 - 15	0	0
Fan Supply	N	-	-	-	-
	N1	24	Fixed	0.2	4.8
	N2	12	6-12	-	3.0
	N3	12	Fixed	0.25	3.0

*576W peak power up to 2 minutes with 500Wrms power using the following formula:

$$500Wrms = ((peakpower^2 \times T1 + reducedpower^2 \times T2)/(T1 + T2))^{1/2}$$

Where T1 = peak power time on in seconds
T2 = reduced power time on in seconds

Non-Standard Models:

X00011#	XMS350-24-NN-N1CBLEN	Customer specific chassis
X00023#	XMS500D-24.5-5C-KFCBDEN	Customer specific top fan/chassis model
X00073#	XMS500-24-NN-NCBRInA	Customer specific chassis/cover

Where # can be any letter denoting non-safety related changes.

Output Limitations:

The following outputs are ES1: 12, 24, 36, 40V

The following outputs are ES2: 48V