

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Switch mode power supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Name and address of the factory	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	100-240 Vac nom, 45-440 Hz 4.7 Arms max see Test Report for details
Trademark / Brand (if any)	TDK-LAMBDA 
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	EFE-300 series, EFE300 Series See Page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include technical modifications. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61010-1:2010
As shown in the Test Report Ref. No. which forms part of this Certificate	E331788-D1004-1/A1/C0-ULCB issued on 2020-08-20

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-08-25

Original Issue Date: 2019-09-11

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-87639-M1-UL

Model Details:

EFE-300 series, EFE300 Series (may be followed by characters as described in Model Differences, see Model Differences in test report for details)

Factories:

PANYU TRIO MICROTRONIC CO LTD
SHIJI INDUSTRIAL ESTATE DONGYONG, NANSHA GUANGZHOU GUANGDONG
CHINA

Additional Information:

The original report was modified to include following changes/additions:

- Addition of alternate discharge resistors XR54, XR55, rated 180 kOhm.

Additionally evaluated to EN 61010-1:2010; National Difference specified in the CB Test Report

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-08-25

Original Issue Date: 2019-09-11

Signature:

Jan-Erik Storgaard