



Ref. Certif. No.

**DK-42330-A1-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

**CB TEST CERTIFICATE**

Product

Power Supply

Name and address of the applicant

TDK-LAMBDA UK LTD  
KINGSLEY AVE  
ILFRACOMBE, EX34 8ES United Kingdom

Name and address of the manufacturer

TDK-LAMBDA UK LTD  
KINGSLEY AVE  
ILFRACOMBE, EX34 8ES United Kingdom

Name and address of the factory

Note: When more than one factory, please report on page 2

Panyu Trio Microtronics Co Ltd  
SHIJI INDUSTRIAL ESTATE  
DONGYONG NANSHA  
GUANGZHOU, 511453 GUANGDONG China

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)

TDK-Lambda



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

NV-700 Range, NV700, RA-PFC-001  
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2:2013; National Differences specified in the CB Test Report

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1, IEC 60950-1(ed.2);am2

As shown in the Test Report Ref. No. which forms part of this Certificate

E135494-A53-CB-3 issued on 2017-04-25

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2017-05-11  
Original Issue Date: 2014-12-10

Signature:

Jan-Erik Storgaard

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)



Ref. Certif. No.

**DK-42330-A1-UL**

**Model Details:**

NV700 or NV-700 Range, RA-PFC-001 (see test report for details of NV700 Range model configurations)

**Factories:**

TDK-LAMBDA UK LTD  
KINGSLEY AVE  
ILFRACOMBE, EX34 8ES United Kingdom

**Ratings:**

NV700 or NV-700 Range:  
100-240Vac nominal (90-264V max. tolerance), 47-440Hz, 11A  
(see test report for details of model ratings)

**RA-PFC-001:**

input: 100-240Vac nominal (90-264V max. tolerance), 47-63Hz, 11A max.  
output: 350Vdc, 2.3A max.

**Additional Information:**

The original report was modified to include the following changes/additions:  
Alternate component to the critical component list

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/incbnames](http://www.ul.com/incbnames)

Date: 2017-05-11  
Original Issue Date: 2014-12-10

Signature:   
Jan-Erik Storgaard