

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI, 940-1195 NIIGATA Japan

Name and address of the manufacturer

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI, 940-1195 NIIGATA Japan

Name and address of the factory

Note: When more than one factory, please report on page 2

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI
TSUKUBA-SHI, 305-0831 IBARAKI-KEN Japan Additional Information on page 2
See Page 2

Ratings and principal characteristics

Trademark (if any)

TDK-Lambda

Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

RWS1500B-12/ME, RWS1500B-15/ME, RWS1500B-24/ME,
RWS1500B-36/ME, RWS1500B-48/ME
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 60601-1: 2006 / A1: 2013 / A12: 2014; National Differences specified in the CB Test Report.

 Additional Information on page 2
IEC 60601-1(ed.3), IEC 60601-1(ed.3);am1

A sample of the product was tested and found to be in conformity with

As shown in the Test Report Ref. No. which forms part of this Certificate

E309264-D1028-1/A0/C0-CB issued on 2017-03-30

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-04-03

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-29556-UL

Model Details:

RWS1500B-12/ME,RWS1500B-15/ME,RWS1500B-24/ME,RWS1500B-36/ME,RWS1500B-48/ME Maybe followed by suffix "abcd" (a is R, b is CO2, c is FO, d is RF; and "a", "b", "c" and "d" may be blank) (for details, see test report)

Factories:

SENDAN ELECTRONICS MFG CO LTD
1010 HABUSHIN
NANTO-SHI, 939-1756 TOYAMA-KEN Japan

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI
NAGAOKA-SHI, 940-1195 NIIGATA-KEN Japan

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI
SENAI, 81400 JOHOR Malaysia

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4
KAWASAN PERINDUSTRIAN
BANDAR BARU JAYA GADING
KUANTAN, 26070 PAHANG Malaysia

Wuxi TDK-Lambda Electronics Co Ltd
NO 6
XING CHUANG ER LU
WUXI, 214028 JIANGSU China

Ratings:

Input: 100-240 Vac, 19.0 A, 50-60 Hz

Output:

- RWS1500B-12/ME: 12 Vdc, 125 A
- RWS1500B-15/ME: 15 Vdc, 100 A
- RWS1500B-24/ME: 24 Vdc, 63 A
- RWS1500B-36/ME: 36 Vdc, 42 A
- RWS1500B-48/ME: 48 Vdc, 32 A

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-04-03

Signature:

Jolanta M. Wroblewska