

UL TEST REPORT AND PROCEDURE

Standard:	UL 60601-1, 1st Edition, 2006-04-26 (Medical Electrical Equipment, Part 1: General Requirements for Safety) CAN/CSA-C22.2 No. 601.1-M90, 2005 (Medical Electrical Equipment - Part 1: General Requirements for Safety)
Certification Type:	Component Recognition
CCN:	QQHM2, QQHM8 (Power Supplies, Medical and Dental)
Product:	Medical Switch Mode Power Supply
Model:	EFE300M Series (see model differences for details of models and nomenclature)
Rating:	100-240Vac nom, 45-63Hz, 4.9A rms max. (see model differences for details of models and ratings)
Applicant Name and Address:	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared by: Ermanno Rebecchi

Reviewed by: Dennis Butcher

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The EFE300M Series are switched mode power supplies for building into host equipment

Model Differences

Nominal Input Voltage Range	100 - 240V AC
Maximum Input Voltage Range	90** - 264V AC
Input Frequency	45-63Hz
Maximum Input Current	4.9A rms

** Channel 1 output is linearly derated from 90Vac to 85Vac, 4W per volt to 280W.

All ratings apply for ambient temperatures up to 50°C. From 50 to 70°C the output power is derated at 2.5% per deg C.

EFE300M or EFE-300M models as described below:

(may be prefixed by NS - # / where # may be any number of characters indicating non safety related model differences)

Products may additionally be marked with U5x or Y5x where x can be any number of characters indicating non-safety related model differences.

Unit Configuration Code: EFE300Mxy-a-b-cdef-ghijk

where:

- x= Nothing or J for Japanese models (may have non-safety differences).
- Y= Blank for Y2 capacitors from output to earth, P for Y1 capacitors from output to earth.
- a= Channel 1 output Voltage: see Ch1 in the outputs table below, adjustment range column.
- b= Standby voltage: see standby voltage table below or 0 for omitted
- c= HN for Open frame, no fan, with 12V / 1A fan supply. HU for U chassis, no fan, with 12V / 1A fan supply. HC for Cover + chassis, no fan, with 12V / 1A fan supply. EC for Cover + chassis, end fan (temp controlled). NN for Open frame, no fan, no fan supply. NU for U chassis, no fan, no fan supply. NC for Cover + chassis, no fan, no fan supply. CN for Open frame, no fan, with 12V / 0.25A fan supply. CU for U chassis, no fan, with 12V / 0.25A fan supply. CC for Cover + chassis, no fan, with 12V / 0.25A fan supply.
- d= M for molex input connector or equivalent, J for JST connector or equivalent.
- e= D for dual fused input or L for single fuse in the live line
- f= S for standard Leakage, L for low Leakage, R for reduced Leakage, T for tiny Leakage. *

g= Y for Oring FET included or N for nothing.
h= E for enable, T for inhibit, N for no inhibit, no enable.
i= Nothing for horizontal output connector, -V for vertical output connector, -S for screw terminal
j= Nothing for standard channel 1 output voltage, -xD or -xPD where D is for units with programmed negative load regulation, PD is for units with programmed positive load regulation, x is the voltage of the regulation in 100mVolts and is within the Output Adjustment range (example, 7D = 0.7V of negative load regulation, 24PD = 2.4V of positive load regulation).
k= Nothing or -x where x is three numbers from 0 to 9 which denotes various output voltage/current settings within the specified ranges of each output for a particular unit or blank for standard output settings. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP)

* L < 300uA leakage, R < 150uA leakage and T < 75uA leakage.

Output parameters:

O/P Channel	Vout nom (V).	Range (V)	Max O/P (A)	Max O/P (W)
CH1	12	11.4 - 13.2*	25	300 (400**)
	24	22.8 - 26.4*	12.5	300 (400**)
	28	27 - 32*	10.72	300 (400**)
	40	36 - 42*	7.5	300 (350***)
	48	47 - 50*	6.25	300 (350***)
	50	50.1 - 54*	6.0	300 (350***)
Standby	5	Fixed	2	10
	12	Fixed	1	12
	13.5	12-13.5*	1	13.5
Fan output	12	Fixed	0.25	3
	12	Fixed	1	12

* Can be adjusted from nominal at the factory only.

** Peak power of 400W for 10 seconds maximum, maximum rms power of 300W:

*** Peak power of 350W for 10 seconds maximum, in any 1 minute cycle, maximum rms power of 300W:

where T1 = peakpower time on
and T2 = reduced power time on

Maximum continuous power output 300W (excluding fan output)

Output Limitations

All standard outputs are SELV up to and including 48V nominal. Voltages above 48V nominal are non SELV and must not be accessible to an end operator..

All outputs have basic spacings to earth, and due consideration must be given to this in the end product design.

Non Standard models.

Model: Y5J008# (where # can be any letter) or EFE300MJ-12.1-5-008 or EFE300MJ-12.1-5-008-SGP

Maximum outputs: 12.1V, 21.49A, plus 5V, 2A standby.

Maximum ambient: As standard model.

Orientations: As standard model.

Comments: Fan speed is controlled at 6600rpm up to and between 45 to 50°C ambient after which the fan

speed increases to typically 10,000rpm (10V). Can be fitted with or without fan guard.

Model: Y5J006# (where # can be any letter) or EFE300MJ-12-5-006.

Maximum outputs: 11.4V to 13.2V*, 25A, (300W max) plus 5V, 2A standby.

Maximum ambient: As standard model.

Orientations: As standard model.

Comments: Longer version than standard model to accommodate additional reservoir capacitor for a greater hold up time.

Model: Y5J015# (where # can be any letter) or EFE300MJ-12.1-5-009 or EFE300MJ-12.1-5-009-SGP

Maximum outputs: 12.1V, 24.79A plus 5V, 2A standby.

Main output may also be 11.4 to 13.2V at 25A max. limited to 300W max.

Maximum ambient: As standard model.

Orientations: As standard model.

Comments: Model is the same as Y5J008# but is a NN.

Technical Considerations

- Classification of installation and use : For building into host equipment
- Supply connection : Connection to mains via host equipment
- Accessories and detachable parts included in the evaluation : None
- Options included : None
- The product was investigated to the following additional standards:: EN 60601-1: 1990 + A1:1993 + A2:1995, UL 60601-1, 1st Edition, 2006-04-26 (includes National Differences for USA), CAN/CSA-C22.2 No. 601.1-M90 (R2005) (includes National Differences for Canada)
- The product was not investigated to the following standards or clauses:: Clause 52.1, Programmable Electronic Systems (IEC 601-1-4), Clause 48, Biocompatibility (ISO 10993-1), Clause 36, Electromagnetic Compatibility (IEC 601-1-2)
- The product is Classified only to the following hazards:: Fire,, Shock
- The degree of protection against harmful ingress of water is:: Ordinary (IPX0)
- The mode of operation is:: Continuous
- The product was submitted and tested for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: 50°C (full load); 70°C (output power decreasing linearly by 2.5%/°C above 50°C)
- The applicant has declared the outputs as SELV for voltages up to and including 48V nominal. Testing has therefore been applied to ensure compliance with the limits specified in clause 2.4.3
- Multi-layer PWB's accepted under CBTR Ref. No. E349607-A23 dated 2014-07-31 and letter report, Enclosure 8-06 of this report.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- Insulation (Separation) between primary - secondary output circuits: Double/Reinforced.
- Insulation (Separation) between primary - earth: BASIC
- Insulation (Separation) between secondary circuits - earth: BASIC (at mains).
- Branch circuit protection required: 16A (20A For North America and Canada)
- The following outputs are considered SELV:All standard outputs are SELV up to and including 48V

nominal. Voltages above 48V nominal are non SELV and must not be accessible to an end operator.. , All outputs have basic spacings to earth, and due consideration must be given to this in the end product design, except for Y50029# which has functional spacings to earth. ,

- Some PWB mounted components are rated at the minimum coating rating of 125°C.
- The client has declared that due to component tolerances, the voltage of the 50V output may exceed the limits of SELV as defined in 2.4.3 (greater than 60Vdc). In the end use equipment, either a level of Supplementary protection must be provided or the end use evaluation should establish an acceptable level of risk where the 50V output is used.
- Consideration should be given to repeating the Earth Leakage Tests in the end use equipment.

Additional Information

This report is a reissue of CBTR Ref. No:E349607-A8-CB-1 dated 2011-11-29 including amendments and corrections with CB test certificate Ref. No: DK-5208-A3-UL dated 2014-06-30. Based on the previously conducted testing and review of the product technical documentation including photos, schematics, wiring diagrams and similar it has been determined that the product continues to comply with the standard. Only the tests listed below were deemed necessary.

Abnormal (Clause 52). Dielectric Voltage Withstand (Clause 20.4) F2, alternative fuse test, non critical part, (not mains input).
Temperature (Clause 42). Alternative fan test.

Additional Standards

The product fulfills the requirements of: EN 60601-1: 1990 + A1:1993 + A2:1995 UL 60601-1, 1st Edition, 2006-04-26 (includes National Differences for USA) CAN/CSA-C22.2 No. 601.1-M90 (R2005) (includes National Differences for Canada)