



Ref. Certif. No.

DK-75861-UL

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME**

CB TEST CERTIFICATE

Product	Medical Switch Mode Power Supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON, EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON, EX34 8ES UNITED KINGDOM
Name and address of the factory	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON, EX34 8ES UNITED KINGDOM
Note: <i>When more than one factory, please report on page 2</i>	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark (if any)	TDK-Lambda
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Vega 450, Vega 650, Vega 900, Vega Lite 550, Vega Lite 750 See Page 2
Additional information (if necessary may also be reported on page 2)	National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60601-1:1988, IEC 60601-1:1988/AMD1:1991, IEC 60601-1:1988/AMD2:1995,
As shown in the Test Report Ref. No. which forms part of this Certificate	E349607-D1008-1/A0/C0-CB issued on 2018-07-27

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2018-08-21

Signature:

For full legal entity names see www.ul.com/nbcnames

Jan-Erik Storgaard



Ref. Certif. No.

DK-75861-UL

Model Details:

Vega 450, Vega 650, Vega 900, Vega Lite 550, Vega Lite 750 (see Model Difference in test report for details of models and nomenclature)

Factories:

PANYU TRIO MICROTRONICS CO LTD
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG 511453
CHINA

Ratings:

Vega 450 and Vega Lite 550.

PSUs with cooling option F and without xEW and xFW options:

Input voltage: 94.5-240 V ac nom., 85-264V ac max., 47-63 Hz, 8.5 A rms max.

All other PSUs:

Input voltage: 100-240 V ac nom., 90-264V ac max., 47-63 Hz, 8.5 A rms max.

Vega 650, Vega Lite 750 and Vega 900.

PSUs with cooling option F and without xEW and xFW options:

Input voltage: 94.5-240 V ac nom., 85-264V ac max., 47-63 Hz, 12 A rms max.

All other models:

Input voltage: 100-240 V ac nom., 90-264V ac max., 47-63 Hz, 11 A rms max.

(See test report for details of ratings)

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-08-21

Signature:

Jan-Erik Storgaard