



Test Report issued under
the responsibility of:



TEST REPORT
IEC 60950-1
Information technology equipment - Safety -
Part 1: General requirements

Report Reference No: 4787000011-1

Date of issue: 2015-11-10

Total number of pages: 97

CB Testing Laboratory: UL Japan, Inc.

Address: 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan

Applicant's name: TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER

Address: R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Test specification:

Standard: IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013

Test procedure: CB Scheme

Non-standard test method: N/A

Test Report Form No.: IEC60950_1F

Test Report Form originator: SGS Fimko Ltd

Master TRF: Dated 2014-02

Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description	Switching Power Supply
Trade Mark	Nemic-Lambda
Manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Model/Type reference	1) LWT30H-5FF 2) LWT30H-522 3) LWT30H-525 4) LWT30H-5FF/SCC 5) LWT30H-522/SCC 6) LWT30H-525/SCC 7) LWT30H-522/FJ
Ratings	Input: AC 100-240V, 1.0A, 50/60 Hz Output : Total Output Power: 30W 1. Model: LWT30H-5FF DC +5V/5.0A, +15V/1.2A, -15V/0.6A 2. Model: LWT30H-522 DC +5V/5.0A, +12V/1.2A, -12V/0.6A 3. Model: LWT30H-525 DC +5V/5.0A, +12V/1.2A, -5V/0.6A 4. Model: LWT30H-5FF/SCC DC+5V/5.0A, +15V/1.2A, -15V/0.6A 5. Model: LWT30H-522/SCC DC +5V/5.0A, +12V/1.2A, -12V/0.6A 6. Model: LWT30H-525/SCC DC +5V/5.0A, +12V/1.2A, -5V/0.6A 7. Model: LWT30H-522/FJ DC+5V/5.0A, +12V/1.2A, -12V/0.6A

Testing procedure and testing location:	
<input checked="" type="checkbox"/> CB Testing Laboratory	Testing location / address..... : UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan
<input type="checkbox"/> Associated CB Test Laboratory	Testing location / address..... :
	Tested by (name + signature)..... : Ayano Matsumoto <i>A. Matsumoto</i>
	Approved by (name + signature) ... : Tetsuo Iwasaki Tetsuo Iwasaki
<input type="checkbox"/> Testing Procedure: TMP/CTF Stage 1	Testing location / address..... :
	Tested by (name + signature)..... : _____
	Approved by (name + signature) ... : _____
<input type="checkbox"/> Testing Procedure: WMT/CTF Stage 2	Testing location / address..... :
	Tested by (name + signature)..... : _____
	Witnessed by (name + signature) .. : _____
	Approved by (name + signature) ... : _____
<input type="checkbox"/> Testing Procedure: SMT/CTF Stage 3 or 4	Testing location / address..... :
	Tested by (name + signature)..... : _____
	Approved by (name + signature) ... : _____
	Supervised by (name + signature). : _____
<input type="checkbox"/> Testing Procedure: RMT	Testing location / address..... :
	Tested by (name + signature)..... : _____
	Approved by (name + signature) ... : _____
	Supervised by (name + signature). : _____

- | |
|---|
| <p>List of Attachments</p> <p>National Differences (24 pages)</p> <p>Enclosures (22 pages)</p> |
|---|

Summary Of Testing

Unless otherwise indicated, all tests were conducted at UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan.

Tests performed (name of test and test clause)	Testing location / Comments
Input: Single-Phase (1.6.2)	
Energy Hazard Measurements (2.1.1.5, 2.1.2, 1.2.8.10)	
Capacitance Discharge (2.1.1.7)	
SELV Reliability Test Including Hazardous Voltage Measurements (2.2.2, 2.2.3, 2.2.4)	
Humidity (2.9.1, 2.9.2, 5.2.2)	
Determination of Working Voltage; Working Voltage Measurement (2.10.2)	
Transformer and Wire /Insulation Electric Strength (2.10.5.13)	
Heating (4.5.1, 1.4.12, 1.4.13)	
Ball Pressure (4.5.5, 4.5)	
Touch Current (Single-Phase; TN/TT System) (5.1, Annex D)	
Electric Strength (5.2.2)	
Component Failure (5.3.1, 5.3.4, 5.3.7)	
Abnormal Operation (5.3.1 - 5.3.9)	
Transformer Abnormal Operation (5.3.3, 5.3.7b, Annex C.1)	
Summary of Compliance with National Differences:	
Countries outside the CB Scheme membership may also accept this report.	
List of countries addressed: CA, DE, DK, EU, FI, GB, SE, SI, US	
The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013	

Copy of Marking Plate - Refer to Enclosure titled Marking Plate for copy.

Test item particulars :

Equipment mobility	for building-in
Connection to the mains	not directly connected to the mains
Operating condition	continuous
Access location	restricted access location
Over voltage category (OVC)	OVC II
Mains supply tolerance (%) or absolute mains supply values	+6%, -10%
Tested for IT power systems	No
IT testing, phase-phase voltage (V)	N/A
Class of equipment	Class I
Considered current rating of protective device as part of the building installation (A)	N/A
Pollution degree (PD)	PD 2
IP protection class	Not rated, indoor use only
Altitude of operation (m)	< 2000 m
Altitude of test laboratory (m)	< 1000 m
Mass of equipment (kg)	Approximately 0.40kg

Possible test case verdicts:

- test case does not apply to the test object: N/A
- test object does meet the requirement: P(Pass)
- test object does not meet the requirement: F(Fail)

Testing:

Date(s) of receipt of test item	2006-05-26, 2010-06-22
Date(s) of Performance of tests	2006-07-10, 2010-07-20 to 2010-08-10

General remarks:

"(see Enclosure #)" refers to additional information appended to the report.
 "(see appended table)" refers to a table appended to the report.
 Throughout this report a point is used as the decimal separator.

Manufacturer's Declaration per Sub Clause 4.2.5 of IEC 60950-1:

The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided Yes

When differences exist, they shall be identified in the General Product Information section.

Name and address of Factory(ies):

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4
KAWASAN PERINDUSTRIAN
BANDAR BARU JAYA GADING
26070 KUANTAN MALAYSIA

Wuxi TDK-Lambda Electronics Co Ltd
NO 6
XING CHUANG ER LU
WUXI
JIANGSU 214028 CHINA

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
TONGXIN RD
ZHAOFENG ECONOMIC DEVELOPMENT ZONE
LEYU TOWN
ZHANGJIAGANG
JIANGSU 215622 CHINA

GENERAL PRODUCT INFORMATION:**Report Summary**

All applicable tests according to the referenced standard(s) have been carried out.

Product Description

Switching power supply for use in general office equipment (host equipment is not specified).

Model Differences

All the models are identical except output voltage, transformer (refer to table 1.5.1), output current and some additional circuit below.

LWT30H-5FF/SCC, LWT30H-522/SCC and LWT30H-522/SCC provided with additional circuit to stabilize the switching frequency. LWT30H-522/FJ provided with additional circuit to have OVP function for two channels.

If not stated otherwise, tests were conducted on model LWT30H-5FF to represent the other similar models.

Additional Information

This report is a reissue of CBTR Ref. No.: 18004363 001, CB Test Certificate Ref. No. JPTUV-046310. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, has been determined that the product continues to comply with the standard.

Abbreviations used in the report.

- built-in application: B/I

In this Test Report, CENELEC mark license indicating compliance to EN standard was used to verify component compliance to IEC standard because the standards are technically equivalent.

It was considered that UL Standard has requirements that meet or exceed the relevant IEC requirements.

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer’s specification of: 40°C
- The product is intended for use on the following power systems: TN
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The end-product Electric Strength Test is to be based upon a maximum working voltage of: max working voltage: 250 Vrms, 483 Vpk
- The following secondary output circuits are SELV: All output
- The power supply terminals and/or connectors are: Suitable for factory wiring only
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Not been conducted
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C): T1 (Class B)
- The following end-product enclosures are required: Fire, Electrical

Abbreviations used in the report:

- normal condition	N.C.	- single fault condition	S.F.C
- operational insulation	OP	- basic insulation	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation	SI
- double insulation	DI	- reinforced insulation	RI

Indicate used abbreviations (if any)