

DK-92750-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Name and address of the applicant

Name and address of the manufacturer

Name and address of the factory

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

Trademark (if any)

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

As shown in the Test Report Ref. No. which forms part of this Certificate

Power Supply

TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM

TDK-LAMBDA UK LTD

KINGSLEY AVE ILFRACOMBE EX34 8ES

UNITED KINGDOM

TDK-LAMBDA UK LTD

KINGSLEY AVE ILFRACOMBE EX34 8ES

UNITED KINGDOM

Additional Information on page 2

Input: 100-240 Vac nominal, (85-264 Vac including tolerances), 47-440 Hz, 5.5

A rms max., AC



TDK-Lambda

NV350 or NV3 or NV-350

Additional Information on page 2

The report was revised to include technical modifications.

Additional Information on page 2

IEC 62368-1:2014

E135494-A6017-CB-1 issued 2021-04-19

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-04-20

Original Issue Date: 2020-01-31

Signature:

Jan-Erik Storgaard





Factories:

PANYU TRIO MICROTRONICS CO LTD SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU, GUANGDONG, 511453 CHINA

Additional Model(s):

Series: NV350 or NV3 or NV-350, (these models are identical) (may be prefixed by NS - # / or - where # may be up to any four letters and may be followed by - \$, where \$ maybe any number between 000 to 999, indicating non-safety related model differences.)

Additionally evaluated to:

EN 62368-1:2014/A11:2017, EN 62368-1:2014

Summary of Modifications:

Update CCL with the addition of 2 alternate Relays: TE Connectivity Relay 2-1416010-6 (RE034012) & Hongfa HF171F12-H3

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-04-20

Original Issue Date: 2020-01-31

Signature: //
Jan-Erik Storgaard