

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Switch-mode power supplies
Name and address of the applicant	TDK-Lambda UK Ltd Kingsley Avenue, Ilfracombe Devon, EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK-Lambda UK Ltd Kingsley Avenue, Ilfracombe Devon, EX34 8ES UNITED KINGDOM
Name and address of the factory	TDK-Lambda UK Ltd Kingsley Avenue, Ilfracombe Devon, EX34 8ES UNITED KINGDOM
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark / Brand (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	CUS100ME, CUS150M, KCUS100ME-32/0001#, See Page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include technical modifications. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005
As shown in the Test Report Ref. No. which forms part of this Certificate	E349607-D1003-2/A1/C0-ULCB issued 2021-03-15

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-03-19

Original Issue Date: 2020-06-19

Signature:

Jan-Erik Storgaard

Model Details:

CUS150M (may be prefixed and followed by alphanumeric characters – See test report model differences section for details of nomenclature).

CUS100ME (may be prefixed and followed by alphanumeric characters – See test report model differences section for details of nomenclature).

KCUS100ME-32/0001# (where # can be any letter or character indicating non-safety related changes).

Factories:

PANYU TRIO MICROTRONIC CO. LTD

SHIJI INDUSTRIAL ESTATE DONGYONG, NANSHA, GUANGZHOU GUANGDONG
CHINA

TDK-Lambda Malaysia Sdn. Bhd.

Lot 2 & 3, Batu 9 3/4, Kawasan Perindustrian Bandar Baru Jaya Gading 26070 Kuantan, Pahang
Malaysia

Ratings:

Input:

CUS150M-xxVx/yyyy

100-240Vac; 47-63Hz; 2.2Arms Max.

CUS150MD-xxVx/yyyy

133-318Vdc, 1.8A

CUS100ME-xxVx/yyyy

100-240Vac; 47-63Hz; 1.4Arms Max.

KCUS100ME-32/0001#

100-240Vac +10%/-20%; 47-63Hz; 1.4Arms Max.

Output:

CUS100ME-12/yyyy output: 12-13.2Vdc 8.33A

CUS100ME-15/yyyy output: 15-16.5Vdc 6.66A

CUS100ME-18/yyyy output: 18-19.8Vdc 5.55A

CUS100ME-24/yyyy output: 24-26.4Vdc 4.16A

CUS100ME-28/yyyy output: 28-30.8Vdc 3.57A

CUS100ME-36/yyyy output: 36-39.6Vdc 2.77A

CUS100ME-48/yyyy output: 48-50Vdc 2.08A

KCUS100ME-32/0001# output: 32.2Vdc 3.11A

CUS150M-12/yyyy output: 12-13.2Vdc 12.5A

CUS150M-15/yyyy output: 15-16.5Vdc 10A

CUS150M-18/yyyy output: 18-19.8Vdc 8.33A

CUS150M-24/yyyy output: 24-26.4Vdc 6.25A

CUS150M-28/yyyy output: 28-30.8Vdc 5.4A

CUS150M-36/yyyy output: 36-39.6Vdc 4.2A

CUS150M-48/yyyy output: 48-50Vdc 3.125A

Each output has a range shown in the table above which is factory configurable only.

For further details please see model differences section.

Class II

Additional Information:

The original report was modified to include following changes/additions:

- update of LoCC. See test report for details.

National Differences specified in the CB Test Report.

The risk management requirements of the standard were not addressed.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-03-19

Original Issue Date: 2020-06-19

Signature:

Jan-Erik Storgaard