

	<p>Test Report issued under the responsibility of:</p>	
---	--	---

<p><b>TEST REPORT</b> <b>IEC 60950-1</b> <b>Information technology equipment - Safety -</b> <b>Part 1: General requirements</b></p>	
<b>Report Reference No</b> .....	4786910624-13
Date of issue .....	2015-09-18
Total number of pages .....	136
<b>CB Testing Laboratory</b> .....	UL Japan, Inc.
Address .....	4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan
<b>Applicant's name</b> .....	TDK-LAMBDA CORP
Address .....	NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
<b>Test specification:</b>	
Standard .....	IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013
Test procedure .....	CB Scheme
Non-standard test method .....	N/A
<b>Test Report Form No.</b> .....	IEC60950_1F
Test Report Form originator .....	SGS Fimko Ltd
Master TRF .....	Dated 2014-02
<p><b>Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.</b></p> <p>This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.</p> <p>If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.</p> <p><b>This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.</b></p>	
<b>General disclaimer</b>	
<p>The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.</p>	

<b>Test item description</b> .....	Switching Power Supply																				
Trade Mark .....	<b><i>TDK·Lambda</i></b> or <b><i>TDK·Lambda</i></b>																				
Manufacturer .....	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN																				
Model/Type reference .....	ZWQ80-5xyz, ZWQ80-5xy2, ZWQ80-5xy4 (series name; ZWQ80 series) x,y =2 or F, z =3,5,B or D may be followed by suffix /L, /A, /FG, /LFG, /AFG, /AC, /LAC																				
Ratings .....	Input: AC 100-240V, 50/60Hz, 1.6A																				
	Output:																				
	<table border="1"> <thead> <tr> <th>Models without /LWQ</th> <th>Output V1</th> <th>Output V2</th> <th>Output V3</th> <th>Output V4</th> </tr> </thead> <tbody> <tr> <td>ZWQ80-5xyB</td> <td rowspan="5">DC 5 – 5.25V, 10.0/8.0A</td> <td rowspan="5">DC 12V, 2.5/2.0A (when x = 2)  DC 15V, 2.5/2.0A (when x = F)</td> <td rowspan="5">DC -12V, 2.5/2.0A (when y = 2)  DC -15V, 2.5/2.0A (when y = F)</td> <td>DC 2V, 9.0/7.0A</td> </tr> <tr> <td>ZWQ80-5xy3</td> <td>DC 2.0 – 3.63V, 9.0/7.0A</td> </tr> <tr> <td>ZWQ80-5xyD</td> <td>DC 4V, 9.0/7.0A</td> </tr> <tr> <td>ZWQ80-5xy5</td> <td>DC 2.0 – 5.25V, 9.0/7.0A</td> </tr> <tr> <td>ZWQ80-5xy2</td> <td>DC 11.4 – 12.6V, 4.0/3.0A</td> </tr> <tr> <td>ZWQ80-5xy4</td> <td>DC 22.8 – 25.2V, 2.0/1.5A</td> </tr> </tbody> </table>	Models without /LWQ	Output V1	Output V2	Output V3	Output V4	ZWQ80-5xyB	DC 5 – 5.25V, 10.0/8.0A	DC 12V, 2.5/2.0A (when x = 2)  DC 15V, 2.5/2.0A (when x = F)	DC -12V, 2.5/2.0A (when y = 2)  DC -15V, 2.5/2.0A (when y = F)	DC 2V, 9.0/7.0A	ZWQ80-5xy3	DC 2.0 – 3.63V, 9.0/7.0A	ZWQ80-5xyD	DC 4V, 9.0/7.0A	ZWQ80-5xy5	DC 2.0 – 5.25V, 9.0/7.0A	ZWQ80-5xy2	DC 11.4 – 12.6V, 4.0/3.0A	ZWQ80-5xy4	DC 22.8 – 25.2V, 2.0/1.5A
Models without /LWQ	Output V1	Output V2	Output V3	Output V4																	
ZWQ80-5xyB	DC 5 – 5.25V, 10.0/8.0A	DC 12V, 2.5/2.0A (when x = 2)  DC 15V, 2.5/2.0A (when x = F)	DC -12V, 2.5/2.0A (when y = 2)  DC -15V, 2.5/2.0A (when y = F)	DC 2V, 9.0/7.0A																	
ZWQ80-5xy3				DC 2.0 – 3.63V, 9.0/7.0A																	
ZWQ80-5xyD				DC 4V, 9.0/7.0A																	
ZWQ80-5xy5				DC 2.0 – 5.25V, 9.0/7.0A																	
ZWQ80-5xy2				DC 11.4 – 12.6V, 4.0/3.0A																	
ZWQ80-5xy4	DC 22.8 – 25.2V, 2.0/1.5A																				
	Max. total output power: 80W for convection cooling 104W for forced air cooling and at peak current																				

<b>Testing procedure and testing location:</b>	
<input checked="" type="checkbox"/> <b>CB Testing Laboratory</b>	Testing location / address .....: UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan
<input type="checkbox"/> <b>Associated CB Test Laboratory</b>	Testing location / address .....:
	Tested by (name + signature).....: Ayano Matsumoto <i>A. Matsumoto</i>
	Approved by (name + signature)....: Tetsuo Iwasaki <b>TetsuoIwasaki</b>
<input type="checkbox"/> <b>Testing Procedure: TMP/CTF Stage 1</b>	Testing location / address .....:
	Tested by (name + signature).....: _____
	Approved by (name + signature)....: _____
<input type="checkbox"/> <b>Testing Procedure: WMT/CTF Stage 2</b>	Testing location / address .....:
	Tested by (name + signature).....: _____
	Witnessed by (name + signature) ..: _____
	Approved by (name + signature)....: _____
<input type="checkbox"/> <b>Testing Procedure: SMT/CTF Stage 3 or 4</b>	Testing location / address .....:
	Tested by (name + signature).....: _____
	Approved by (name + signature)....: _____
	Supervised by (name + signature) ..: _____
<input type="checkbox"/> <b>Testing Procedure: RMT</b>	Testing location / address .....:
	Tested by (name + signature).....: _____
	Approved by (name + signature)....: _____
	Supervised by (name + signature) ..: _____

<b>List of Attachments</b>
National Differences ( 24 pages)
Enclosures ( 56 pages)
<b>Summary Of Testing</b>
Unless otherwise indicated, all tests were conducted at UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan.

Tests performed (name of test and test clause)	Testing location / Comments
Input: Single-Phase (1.6.2)	
Capacitance Discharge (2.1.1.7)	
SELV Reliability Test Including Hazardous Voltage Measurements (2.2.2, 2.2.3, 2.2.4)	
Humidity (2.9.1, 2.9.2, 5.2.2)	
Determination of Working Voltage; Working Voltage Measurement (2.10.2)	
Transformer and Wire /Insulation Electric Strength (2.10.5.13)	
Heating (4.5.1, 1.4.12, 1.4.13)	
Ball Pressure (4.5.5, 4.5)	
Touch Current (Single-Phase; TN/TT System) (5.1, Annex D)	
Electric Strength (5.2.2)	
Component Failure (5.3.1, 5.3.4, 5.3.7)	
Abnormal Operation (5.3.1 - 5.3.9)	
Transformer Abnormal Operation (5.3.3, 5.3.7b, Annex C.1)	
Power Supply Output Short-Circuit/Overload (5.3.7)	
<p><b>Summary of Compliance with National Differences:</b>  Countries outside the CB Scheme membership may also accept this report.  List of countries addressed: CA, DE, DK, EU, FI, GB, KR, SE, SI, US  The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013</p>	

**Copy of Marking Plate** - Refer to Enclosure titled Marking Plate for copy.

<b>Test item particulars :</b>	
Equipment mobility .....	for building-in
Connection to the mains .....	not directly connected to the mains
Operating condition .....	continuous
Access location .....	N/A
Over voltage category (OVC) .....	OVC II
Mains supply tolerance (%) or absolute mains supply values .....	-10%, +6%
Tested for IT power systems .....	Yes
IT testing, phase-phase voltage (V) .....	230V
Class of equipment .....	Not classified, class I construction
Considered current rating of protective device as part of the building installation (A) .....	Not considered (built-in application)
Pollution degree (PD) .....	PD 2
IP protection class .....	Not rated.
Altitude of operation (m) .....	≤ 2000m
Altitude of test laboratory (m) .....	< 1000m
Mass of equipment (kg) .....	0.55kg
<b>Possible test case verdicts:</b>	
- test case does not apply to the test object .....	N/A
- test object does meet the requirement .....	P(Pass)
- test object does not meet the requirement .....	F(Fail)
<b>Testing:</b>	
Date(s) of receipt of test item .....	N/A
Date(s) of Performance of tests .....	2004-10 to 2004-11, 2007-07 to 2007-08
<b>General remarks:</b>	
<p>"(see Enclosure #)" refers to additional information appended to the report.                  "(see appended table)" refers to a table appended to the report.</p> <p>Throughout this report a point is used as the decimal separator.</p>	
<b>Manufacturer's Declaration per Sub Clause 4.2.5 of IEC60950:</b>	
The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided .....	Yes
When differences exist, they shall be identified in the General Product Information section.	
<b>Name and address of Factory(ies):</b>	TDK-LAMBDA CORP 2704-1 SETTAYA-MACHI

NAGAOKA-SHI  
NIIGATA-KEN 940-1195 JAPAN

TDK-LAMBDA MALAYSIA SDN BHD  
PLO33 KAWASAN PERINDUSTRIAN SENAI  
81400 SENAI MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD  
LOT 2 & 3, BATU 9 3/4  
KAWASAN PERINDUSTRIAN  
BANDAR BARU JAYA GADING  
26070 KUANTAN MALAYSIA

ALPS LOGISTICS FACILITIES CO LTD  
593-1 NISHIOHASHI  
TSUKUBA-SHI  
IBARAKI-KEN 305-0831 JAPAN

Wuxi TDK-Lambda Electronics Co Ltd  
NO 6  
XING CHUANG ER LU  
WUXI  
JIANGSU 214028 CHINA

SENDAN ELECTRONICS MFG CO LTD  
1010 HABUSHIN  
NANTO-SHI  
TOYAMA-KEN 939-1756 JAPAN

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD  
TONGXIN RD  
ZHAOFENG ECONOMIC DEVELOPMENT ZONE  
LEYU TOWN  
ZHANGJIAGANG  
JIANGSU 215622 CHINA

#### **GENERAL PRODUCT INFORMATION:**

##### **Report Summary**

All applicable tests according to the referenced standard(s) have been carried out.

##### **Product Description**

The product testes is built-in type switching power supply for use in general office equipment (host equipment is not specified).

##### **Model Differences**

All models are identical to each other except for output rating, winding of transformer T1, and minor primary and secondary components.

Definition of variable(s):

Variable:	Range of variable:	Content:
x	2, F	2: Output voltage of V2; DC 12V F: Output voltage of V2; DC 15V
y	2, F	2: Output voltage of V3; DC -12Vdc F: Output voltage of V3; DC -15V
z	B, 3, D, 5,	Output voltage of output V4 (see page 2)
Optional suffix	/L, /A, /FG, /LFG, /AFG, /AC, /LAC or blank	Blank: basic model (PWB type SWPS) /L : denotes models with chassis provided /A : denotes models with chassis and cover provided /FG: denotes models with capacitors (C2, C3) rated less than 1000pF and capacitor (C8) rated less than 4700pF. /LFG: denote models combination of /L and /FG /AFG: denote models combination of /A and /FG /AC: denotes models with direction of input connector changed. /LAC: denotes models with optional chassis provided and direction of input connector changed.

**Additional Information**

This report is a reissue of CBTR Ref. No.: 12027279 001, CB Test Certificate Ref. No.JPTUV-045940. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, has been determined that the product continues to comply with the standard.

Sample Received date is 2000-05-17.  
Construction review was conducted on 2000-05-17.

Abbreviations used in the report.  
- built-in application: B/I

In this Test Report, CENELEC mark license indicating compliance to EN standard was used to verify component compliance to IEC standard because the standards are technically equivalent.

It was considered that UL Standard has requirements that meet or exceed the relevant IEC requirements.

**Technical Considerations**

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer’s specification of: See enclosure Id 7-03.
- The product is intended for use on the following power systems: TN
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).

**Engineering Conditions of Acceptability**

When installed in an end-product, consideration must be given to the following:

- The end-product Electric Strength Test is to be based upon a maximum working voltage of: max working voltage: 536 Vrms 832 Vpk
- The following secondary output circuits are SELV: All output
- The power supply terminals and/or connectors are: Suitable for factory wiring only
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Not been conducted
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C): T1 (Class B)
- The following end-product enclosures are required: Fire, Electrical

Abbreviations used in the report:

- normal condition .....	N.C.	- single fault condition.....	S.F.C
- operational insulation .....	OP	- basic insulation .....	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation .....	SI
- double insulation .....	DI	- reinforced insulation .....	RI

Indicate used abbreviations (if any)