

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE**CERTIFICAT D'ESSAI OC**

Product
Produit

Switching Power Supply

Name and address of the applicant
Nom et adresse du demandeur

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Name and address of the manufacturer
Nom et adresse du fabricant

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Name and address of the factory
Nom et adresse de l'usine

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} page

Additional Information on page 2

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

See Page 2

Trademark (if any)
Marque de fabrique (si elle existe)



Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais
constructeur

Model / Type Ref.
Ref. De type

HWS1500-xy
See Page 2

Additional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,,
peuvent être indiqués sur la 2^{ème} page

Additionally evaluated to
EN 60950-1:2006/A11:2009/A1:2010/A12:2011/A2:2013
National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60950-1 (ed.2), IEC 60950-1 (ed.2);am1,
IEC 60950-1 (ed.2);am2

As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

4786910622-4 issued on 2015-08-03

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-08-11

Signature:

Yoshihiro Yamamoto



Ref. Certif. No.

JP-12587-UL

Model Details:

HWS1500-xy

x = 3, 5, 6, 7, 12, 15, 24, 36, 48, 60

y = /CO, /HD, /LNF (for x=24, 36, 48), /LNF3K (for x=24), or blank (for all suffix x)

Factories:

TDK-LAMBDA MALAYSIA SDN BHD

PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD

LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN MALAYSIA

ALPS LOGISTICS FACILITIES CO LTD

593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831 JAPAN

Wuxi TDK-Lambda Electronics Co Ltd

NO 6 XING CHUANG ER LU WUXI JIANGSU 214028 CHINA

SENDAN ELECTRONICS MFG CO LTD

1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756 JAPAN

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD

TONGXIN RD ZHAOFENG ECONOMIC DEVELOPMENT ZONE LEYU TOWN

ZHANGJIAGANG JIANGSU 215622 CHINA

Ratings:

Input:

AC 100-240 V, 50/60 Hz,

15 A for model HWS1500-3y

20 A for other models

Output:

HWS1500-3y: 3.3Vdc (2.64 – 3.96 Vdc), 300 A (max. 990 W)

HWS1500-5y: 5Vdc (4.0 – 6.0 Vdc), 300 A (max. 1500 W)

HWS1500-6y: 6Vdc (4.8 – 7.2 Vdc), 250 A (max. 1500 W)

HWS1500-7y: 7.5Vdc (6.0 – 9.0 Vdc), 200 A (max. 1500 W)

HWS1500-12y: 12Vdc (9.6 – 14.4 Vdc), 125 A (max. 1500 W)

HWS1500-15y: 15Vdc (12.0 – 18.0 Vdc), 100 A (max. 1500 W)

HWS1500-24y: 24Vdc (19.2 – 28.8 Vdc), 65 A (max. 1560 W) when input is 100-180 Vac and 70 A (max. 1680 W) when input is 180-240 Vac, also following peak output applied: peak current 105 A (max. 2520 W), max. 10 sec., duty 35% when input is 180-240 Vac.

HWS1500-36y: 36Vdc (28.8 – 43.2 Vdc), 42 A (max. 1512 W) when input is 100-180 Vac and 46.5 A (max. 1674 W) when input is 180-240 Vac, also following peak output applied: peak current 70 A (max. 2520 W), max. 10 sec., duty 35% when input is 180-240 Vac.

HWS1500-48y: 48Vdc (38.4 – 52.8 Vdc), 32 A (max. 1536 W)

HWS1500-60y: 60Vdc (48 – 66 Vdc), 25.6 A (max. 1536 W) when input is 100-180 Vac and 28 A (max. 1680 W) when input is 180-240 Vac, also following peak output applied: peak current 42 A (max. 2520 W), max. 10 sec., duty 35% when input is 180-240 Vac.

Additional information (if necessary)

Information complémentaire (si nécessaire)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-08-11

Signature:

Yoshihiro Yamamoto