

	<p>Test Report issued under the responsibility of:</p>	
---	---	---

**TEST REPORT
IEC 60950-1
Information technology equipment - Safety -
Part 1: General requirements**

Report Reference No : 4787989179
Date of issue : 2017-05-23
Total number of pages : 9

CB Testing Laboratory : UL Japan, Inc.
Address : 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan

Applicant's name : TDK-LAMBDA CORP
 NAGAOKA TECHNICAL CENTER
Address : R&D DIV
 2704-1 SETTAYA-MACHI
 NAGAOKA-SHI
 NIIGATA 940-1195 JAPAN

Test specification:
Standard : IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013
Test procedure : CB Scheme
Non-standard test method : N/A

Test Report Form No. : IEC60950_1F
Test Report Form originator : SGS Fimko Ltd
Master TRF : Dated 2014-02


Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer
 The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description	Switching Power Supply
Trade Mark	
Manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Model/Type reference	1) CN100A110-xyza, 2) CN30A110-xyza, 3) CN50A110-xyza (x = 5, 12, 15, 24 denotes output voltage, y = “/” or blank, z = “CO” or blank, a = “T” or blank)
Ratings	Input: 1) 60-160Vdc, 2.5A 2) 60-160Vdc, 0.65A 3) 60-160Vdc, 1.1A Output: 1) 5Vdc, 20A 12Vdc, 8.4A 15Vdc, 6.7A 24Vdc, 4.2A 2) 5Vdc, 6A 12Vdc, 2.5A 15Vdc, 2A 24Vdc, 1.3A 3) 5Vdc, 10A 12Vdc, 4.2A 15Vdc, 3.4A 24Vdc, 2.1A

Testing procedure and testing location:	
<input checked="" type="checkbox"/> CB Testing Laboratory	UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan Testing location / address
<input type="checkbox"/> Associated CB Test Laboratory	Testing location / address
	Tested by (name + signature): Ayano Matsumoto, Project Handler <i>A. Matsumoto</i>
	Approved by (name + signature).....: Tetsuo Iwasaki, Reviewer Tetsuo Iwasaki
<input type="checkbox"/> Testing Procedure: TMP/CTF Stage 1	Testing location / address: Tested by (name + signature): Approved by (name + signature).....:
<input type="checkbox"/> Testing Procedure: WMT/CTF Stage 2	Testing location / address: Tested by (name + signature): Witnessed by (name + signature) ..: Approved by (name + signature).....:
<input type="checkbox"/> Testing Procedure: SMT/CTF Stage 3 or 4	Testing location / address: Tested by (name + signature): Approved by (name + signature).....: Supervised by (name + signature) .:
<input type="checkbox"/> Testing Procedure: RMT	Testing location / address: Tested by (name + signature): Approved by (name + signature).....: Supervised by (name + signature) .:

List of Attachments
 National Differences (0 pages)
 Enclosures (2 pages)

Summary Of Testing
 No tests were conducted
 .

Summary of Compliance with National Differences:

Countries outside the CB Scheme membership may also accept this report.

List of countries addressed: AR, AT, AU, BE, BY, CA, CH, CN, CZ, DE, DK, ES, EU, FI, FR, GB, HU, IL, IT, JP, MY, NL, NO, NZ, PL, RS, RU, SA, SE, SG, SI, SK, TR, UA, US

The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013

Copy of Marking Plate - Refer to Enclosure titled Marking Plate for copy.

Test item particulars :	
Equipment mobility	for building-in
Connection to the mains	not directly connected to the mains
Operating condition	continuous
Access location	N/A
Over voltage category (OVC)	OVC II
Mains supply tolerance (%) or absolute mains supply values	N/A
Tested for IT power systems	No
IT testing, phase-phase voltage (V)	--
Class of equipment	Not classified
Considered current rating of protective device as part of the building installation (A)	N/A
Pollution degree (PD)	PD 2
IP protection class	Not rated, indoor use only
Altitude of operation (m)	≤ 2000 m
Altitude of test laboratory (m)	< 1000 m
Mass of equipment (kg)	approx. 0.1kg
Possible test case verdicts:	
- test case does not apply to the test object	N/A
- test object does meet the requirement	P(Pass)
- test object does not meet the requirement	F(Fail)
Testing:	
Date(s) of receipt of test item	N/A
Date(s) of Performance of tests	N/A
General remarks:	
<p>"(see Enclosure #)" refers to additional information appended to the report. "(see appended table)" refers to a table appended to the report.</p> <p>Throughout this report a point is used as the decimal separator.</p>	
Manufacturer's Declaration per Sub Clause 4.2.5 of IEC60950-1:	
The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided	Yes
When differences exist, they shall be identified in the General Product Information section.	
Name and address of Factory(ies):	TDK-LAMBDA CORP 2704-1 SETTAYA-MACHI

NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI
81400 SENAI MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4
KAWASAN PERINDUSTRIAN
BANDAR BARU JAYA GADING
26070 KUANTAN MALAYSIA

WUXI TDK-LAMBDA ELECTRONICS CO LTD
NO 6 XING CHUANG ER LU
WUXI
JIANGSU 214028 CHINA

GENERAL PRODUCT INFORMATION:

Report Summary

This report is only valid in conjunction with CB Test Report Ref. No. 4786910624-2, including CB Test Report Ref. No. 4787853161 (Amendment 1).

Amendment 2 covers following modification:

Addition of Model with suffix "T".

No tests were considered necessary on models with suffix "T" because of similarity in construction to previously evaluated units.

Product Description

The product tested is a Built-in type Switching Power Supply for use in a general office environment (host equipment is not specified).

Aluminum baseplate PCB is used for mounting the power components and securing a external heatsink. Product must be needed the following external components of the circuit functions and heatsink:

- Input Fuse, rated 400V, 5A
- Input Filter
- Electrolytic Capacitor(s) for the rectifying circuits of primary
- Smoothing electrolytic capacitor(s) for output circuits
- Heatsink secured on the product

In order to maintain SELV output, baseplate must be protectively earthed in the end use application.

Where the baseplate is not earthed, output must be considered hazardous.

Products have been assessed for use with non-isolated mains derived DC supply where the mains source is up to 115Vac. For mains derived DC above 115Vac source of supply and up to 250Vac, there must be isolated equivalent to reinforced insulation at the rated mains voltage source.

Instruction Manual provided.

Relevant tests were performed in the most severe condition allowed by the installation instruction.

The outputs were operated at rated load.

Model Differences

Models CN30A110-x, CN50A110-x (x = 5, 12, 15, 24 for output voltage) are identical to model CN100A110-x, except for input current rating, output current rating, model name, primary coil (L101) and secondary coil (L151) with matching of current. No PCB pattern layout and transformer changed, not affecting safety.

Difference between the models:

Function \ Model	CN100A110-5	CN100A110-12, -15, -24
Output Voltage / Current	5Vdc / 20A	12Vdc / 8.4A, 15Vdc / 6.7A, 24Vdc / 4.2A
Output Voltage range	-10%, +20% 5Vdc (4.5Vdc – 6Vdc)	± 10% 12Vdc (10.8Vdc – 13.2Vdc) 15Vdc (13.5Vdc – 16.5Vdc) 24Vdc (21.6Vdc – 26.4Vdc)
Main Transformer (reinforced)	T102 with control winding of FET	T102
Control Transformer (reinforced)	T1	--
Max. output power	100W	12Vdc / 100.8W, 15Vdc / 100.5W, 24Vdc / 100.8W

Function \ Model	CN30A110-5	CN30A110-12, -15, -24
Output Voltage / Current	5Vdc / 6A	12Vdc / 2.5A, 15Vdc / 2A, 24Vdc / 1.3A
Output Voltage range	-10%, +20% 5Vdc (4.5Vdc – 6Vdc)	± 10% 12Vdc (10.8Vdc – 13.2Vdc) 15Vdc (13.5Vdc – 16.5Vdc) 24Vdc (21.6Vdc – 26.4Vdc)
Main Transformer (reinforced)	T102 with control winding of FET	T102
Control Transformer (reinforced)	T1	--
Max. output power	30W	12Vdc / 30W, 15Vdc / 30W, 24Vdc / 31.2W

Model	CN50A110-5	CN50A110-12, -15, -24
Function		
Output Voltage / Current	5Vdc / 10A	12Vdc / 4.2A, 15Vdc / 3.4A, 24Vdc / 2.1A
Output voltage range	-10%, +20% 5Vdc (4.5Vdc – 6Vdc)	±10% 12vdc (10.8Vdc – 13.2Vdc) 15Vdc (13.5Vdc – 16.5Vdc) 24Vdc (21.6Vdc – 26.4Vdc)
Main Transformer (reinforced)	T102 with control winding of FET	T102
Control Transformer (reinforced)	T1	--
Max. output power	50W	12Vdc/50.4W, 15Vdc/51W, 24Vdc/50.4W

When using output voltage range, equipment shall be used within max output power.

Definition of variable(s):

Variable:	Range of variable:	Content:
x	5, 12, 15, 24	Output voltage
y	"/" or blank	Separator
z	"CO" or blank	CO: PCBs coated with "Humi Seal 1B58LU-60"
a	"T" or blank	T: no threads in the corner

Additional Information

Abbreviations used in the report.

- built-in application: B/I

In addition, following National Differences were considered:

- Russian Federation (RU)**,
- Turkey (TR)**.
- Serbia (RS)**

Note) **: Only Group Differences.

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of: 100°C at the baseplate PCB.
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those

specified in this test report).

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The following secondary output circuits are SELV: All output
- The power supply terminals and/or connectors are: Suitable for factory wiring only
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Not been conducted
- The following end-product enclosures are required: Fire, Electrical

Abbreviations used in the report:

- normal condition	N.C.	- single fault condition	S.F.C
- operational insulation	OP	- basic insulation	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation	SI
- double insulation	DI	- reinforced insulation	RI

Indicate used abbreviations (if any)