

MTBF

The following table shows calculated MTBF (Mean Time Between Failure) values in failures per million hours (fpmh) in accordance with MIL-HDBK-217F Notice 1 for Alpha converters, modules, and options at 25°C and 50°C ambient temperatures.

Module	Failure Rate/ fpmh Ambient = 25C	Failure Rate/ fmpm Ambient = 50C
Alpha 400 Converter, filter (all types), fan (x1)	6.83	11.4
Alpha 600 Converter, filter (all types), fan (x1)	9.83	13.85
Alpha 1000 Converter, filter (all types), fans (x2)	14.0	23.15
Alpha 1500 Coverter, filter (all types), fans (x2)	14.27	23.66
A Module	0.80	1.17
AA Module	1.12	1.91
B Module	0.90	1.31
BB Module	0.97	1.51
C Module	0.84	1.20
D Module	0.82	1.17
E Module	1.25	1.75
EB Module	1.34	2.10
EQ Module	1.51	2.23
F Module,FF Module	0.96	1.35
G Module	0.83	1.12
H Module	1.62	2.30
J Module	1.07	1.62
K Module	0.84	1.22
L Module	1.12	1.63
M Module	0.84	1.18
N Module	0.78	1.10
P Module	1.64	2.33
Q Module	0.55	0.78
R Module	0.82	1.27
S Module	1.42	2.32
T Module	1.36	1.85
U Module	1.06	1.61
W Module	1.09	1.52
Z Module	0.90	1.31

INH Option	0.80	1.10
PA Option	1.12	1.60
PP Option	0.29	0.55
RP Option	0.05	0.06
CD Option	0.45	0.58
MF Option	0.51	0.74
MFL Option	0.66	0.86
MFE Option	0.62	0.80
MFU Option	0.60	0.78

MTBF Calculation

To calculate MTBF for a particular product configuration, sum the failure rates (fpmh) for the individual parts to produce a total failure rate.

MTBF is then simply given by $1,000,000 / \text{fpmh}$.

Example

Product configuration : CA400 24G, 5B, 12C_INH, 24D

Total failure rate is given by summing the individual part failure rates:

CA400 converter 6.83 fpmh

G Module 0.83 fpmh

Module 0.84 fpmh

Option 0.80 fpmh

D Module 0.82 fpmh

Total failure rate 10.12fpmh

MTBF = $1,000,000 / 10.12 = 98,814$ Hours

NB

To exclude MTBF of cooling fan(s), subtract 4.09 fpmh (at 25DegC) or 7.51 fpmh (at 50DegC) for each fan from the total failure rate before calculating the MTBF.

E.g. above configuration excluding fan, Failure rate = $10.12 - 4.09 = 6.03$ fpmh.

C
INH