



Test Report issued under  
the responsibility of:



**TEST REPORT**  
**IEC 60950-1**  
**Information technology equipment - Safety -**  
**Part 1: General requirements**

**Report Reference No** .....: E135494-A33-CB-4

Date of issue .....: 2015-03-27

Total number of pages .....: 28

**CB Testing Laboratory** .....: UL International Demko A/S

Address .....: Borupvang 5A, 2750 Ballerup, Denmark

**Applicant's name** .....: TDK-LAMBDA UK LTD

Address .....: KINGSLEY AVE  
ILFRACOMBE  
DEVON  
EX34 8ES UNITED KINGDOM

**Test specification:**

Standard .....: IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013

Test procedure .....: CB Scheme

Non-standard test method .....: N/A

**Test Report Form No.** .....: IEC60950\_1F

Test Report Form originator .....: SGS Fimko Ltd

Master TRF .....: Dated 2014-02

**Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.**

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

**This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.**

**General disclaimer**

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

<b>Test item description</b> .....	Power Supply
Trade Mark .....	TDK-Lambda
	
Manufacturer .....	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Model/Type reference .....	EFE300 series ( EFE300x-a-bcde- f-g-hij, see model differences for details of models and nomenclature).
Ratings .....	133-318Vdc nom 100-240Vac nom, 45-440Hz 4.7A rms max, 3.8Adc max.

<b>Testing procedure and testing location:</b>	
<input type="checkbox"/>	<b>CB Testing Laboratory</b> Testing location / address .....:
<input type="checkbox"/>	<b>Associated CB Test Laboratory</b> Testing location / address .....: Tested by (name + signature) .....: Approved by (name + signature).....:
<input type="checkbox"/>	<b>Testing Procedure: TMP/CTF Stage 1</b> Testing location / address .....: Tested by (name + signature) .....: Approved by (name + signature).....:
<input type="checkbox"/>	<b>Testing Procedure: WMT/CTF Stage 2</b> Testing location / address .....: Tested by (name + signature) .....: Witnessed by (name + signature) ...: Approved by (name + signature).....:
<input checked="" type="checkbox"/>	<b>Testing Procedure: SMT/CTF Stage 3 or 4</b> Testing location / address .....: TDK-Lambda UK Ltd, Kingsley Avenue, Ilfracombe, Devon, EX34 8ES, United Kingdom Tested by (name + signature) .....: M.Carter - tester Witnessed by (name + signature) ...: Dennis Butcher - witness Approved by (name + signature).....: T.Burgess - approver Supervised by (name + signature) ..: Dennis Butcher/Reviewer

<b>List of Attachments</b>	
National Differences (0 pages)	
Enclosures (38 pages)	
<b>Summary Of Testing</b>	
Unless otherwise indicated, all tests were conducted at TDK-Lambda UK Ltd, Kingsley Avenue, Ilfracombe, Devon, EX34 8ES, United Kingdom.	
<b>Tests performed (name of test and test clause)</b>	<b>Testing location / Comments</b>
End Product Reference Page	
Capacitance Discharge (2.1.1.7)	

Heating (4.5.1, 1.4.12, 1.4.13)

Component Failure (5.3.1, 5.3.4, 5.3.7)

**Summary of Compliance with National Differences:**

Countries outside the CB Scheme membership may also accept this report.

List of countries addressed: AR, AT, AU, BE, BG, BY, CA, CH, CS, CZ, DE, DK, ES, EU, FI, FR, GB, GR, HU, IE, IL, IN, IT, JP, KR, MY, NL, NO, NZ, PL, PT, RO, SA, SE, SI, SK, UA, US, ZA

The product fulfills the requirements of: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2: 2013, CSA C22.2 NO. 60950-1-07 + AMD 1 AMD 2 - Edition 2 - Revision Date 2014/10/14

**Copy of Marking Plate** - Refer to Enclosure titled Marking Plate for copy.

**Test item particulars :**

Equipment mobility .....	for building-in
Connection to the mains .....	To be determined in the end use application
Operating condition .....	continuous
Access location .....	for building in
Over voltage category (OVC) .....	OVC II
Mains supply tolerance (%) or absolute mains supply values .....	90-264Vac or 120-350Vdc
Tested for IT power systems .....	Yes (Norway only)
IT testing, phase-phase voltage (V) .....	230V
Class of equipment .....	Class I (earthed)
Considered current rating of protective device as part of the building installation (A) .....	20A
Pollution degree (PD) .....	PD 2
IP protection class .....	IP X0
Altitude of operation (m) .....	3000m
Altitude of test laboratory (m) .....	64m
Mass of equipment (kg) .....	0.8kg

**Possible test case verdicts:**

- test case does not apply to the test object ..... : N / A
- test object does meet the requirement ..... : P(Pass)
- test object does not meet the requirement ..... : F(Fail)

**Testing:**

Date(s) of receipt of test item .....	2019-06-03, 2019-08-02
Date(s) of Performance of tests .....	2019-08-06 to 2019-08-15

**General remarks:**

"(see Enclosure #)" refers to additional information appended to the report.  
 "(see appended table)" refers to a table appended to the report.

Throughout this report a point is used as the decimal separator.

**Manufacturer's Declaration per Sub Clause 4.2.5 of IEC 60950-1:**

Yes

The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided .....

When differences exist, they shall be identified in the General Product Information section.

**Name and address of Factory(ies):** TDK-LAMBDA UK LTD  
 KINGSLEY AVE  
 ILFRACOMBE  
 DEVON  
 EX34 8ES UNITED KINGDOM

PANYU TRIO MICROTRONIC CO. LTD  
SHIJI INDUSTRIAL ESTATE  
DONGYONG  
NANSHA  
GUANGZHOU GUANGDONG CHINA

TDK-LAMBDA CORP  
2704-1 SETTAYA-MACHI  
NAGAOKA-SHI  
NIIGATA-KEN 940-1195 JAPAN

## GENERAL PRODUCT INFORMATION:

### Report Summary

The original report was modified on 2019-12-27 to include the following changes/additions:

Technical Amendment:

1. Additional discharge resistors added
2. Adding/removing alternates, making corrections and updating component Certificates in the Critical Components list.
3. Enclosures updated where applicable.

Based on conducted testing and review of product construction, it was determined that the product continues to comply with the standard.

This report is an amendment of CBTR Ref. No. E135494-A33-CB-4, CB Test Certificate Ref. No. DK-44432-M1-UL dated 2015-03-27. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, it has been determined that the product continues to comply with the standard with only limited testing being required.

### Product Description

EFE300 range. Switch mode power supplies for building into end equipment.

### Model Differences

Nominal Input Voltage Range	100 - 240V AC or 133 - 318VDC
Maximum Input Voltage Range	90* - 264V AC or 120 - 350VDC
Input Frequency	45-440 Hz maximum or DC
Maximum Input Current	4.7A rms or 3.8A DC

\* Channel 1 output is linearly derated from 90Vac to 85Vac, 4W per volt to 280W.

All ratings apply for ambient temperatures up to 50°C. From 50 to 70°C the output power is derated at 2.5% per deg C.

Unit Configuration Code:

EFE300 or EFE-300x-a-bcde- f-g-hij

(may be prefixed by NS - # / where # may be any number of characters indicating non safety related model differences). Products may additionally be marked with U2x or Y2x where x can be any number of characters indicating non-safety related model differences.

May be prefixed by SP followed by / or - (SP represents a sales code)

where:

x=Nothing or J for Japanese models (may have non-safety differences)

a=Channel 1 Output Voltage: any voltage within the Adjustment Range for the Vout (nom) from the Output Table below, e.g. 12.8 for 12.8V output (12Vout nom), 24.6 for 24.6V output (24Vout nom).

b=CN for Open Frame with fan output, CU for U chassis with fan output, CC for U chassis and cover with fan output, EC for U chassis and cover with fan.

c=M for Molex input connector or equivalent, J for JST connector or equivalent.

d=D for dual fused input or L for single fuse in the live line.

e=S for Standard Leakage, L for Low Leakage, R for Reduced Leakage, T for Tiny Leakage.\*

f=Nothing for horizontal output connector, V for vertical output connector.

g=Nothing for standard channel 1 output voltage, xD or xPD where D is for units with programmed negative load regulation, PD is for units with programmed positive load regulation, x is the voltage of the regulation in 100mVolts and is within the Output Adjustment range (example, 7D = 0.7V of negative load regulation, 24PD = 2.4V of positive load regulation).

hij=Three numbers from 0 to 9 which denotes various output voltage/current settings within the specified ranges of each output for a particular unit or blank for standard output settings. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP)

\* At 440Hz, leakage current is > 3.5mA and therefore must be assessed in the end use application.

\* L < 300uA leakage, R < 150uA leakage and T < 75uA leakage.

Output parameters:

O/P Channel	Vout nom (V).	Range (V)	Max O/P (A)	Max O/P (W)
CH1	12	11.4 - 13.2*	25	300 (400**)
	24	22.8 - 26.4*	12.5	300 (400**)
Fan output	12	Fixed	0.25	3

\* Can be adjusted from nominal at the factory only.

\*\* Peak power of 400W for 10 seconds maximum, maximum rms power of 300W

Maximum continuous power output 300W (excluding fan output)

Output Limitations

All outputs are SELV

All outputs have functional spacing's to earth, and due consideration must be given to this in the end product.

Customer Air Cooling (CN, CU and CC options):

The following method must be used for determining the safe operation of PSUs. The components listed in the following table must not exceed the temperatures given. To determine the component temperatures the heating tests must be conducted in accordance with the requirements of the standard concerned.

Test requirements include: PSU to be fitted in its end-use equipment and operated under the most adverse conditions permitted in the end-use equipment handbook/specification and which will result in the highest temperatures in the PSU. To determine the most adverse conditions consideration should be given to the end use equipment maximum operating ambient, the PSU loading and input voltage, ventilation, end use equipment orientation, the position of doors & covers, etc. Temperatures should be monitored using type K fine wire thermocouples (secured with cyanoacrylate adhesive, or similar) placed on the hottest part of the component (out of any direct airflow) and the equipment should be run until all temperatures have stabilised.

Circuit Ref.	Description	Max. Temperature (°C)
J1	Input connector	75
L1, L2	Common mode choke winding	115 (130)
C7, C8	X capacitors	100
C9	Reservoir capacitor (electrolytic)	60 (105)
L3	Boost choke winding	115 (140)
TX2	Transformer winding	120 (130)
TX2	Transformer core	120 (130)
TX2	Transformer braid	120 (130)
U2	Optocoupler	75 (100)
C10, C11	Channel 1 output capacitors	80 (105)
L6	Primary choke (24V model only)	120 (130)
L4	Channel 1 Output choke	115 (130)
XU2/XU8	Fan regulator	115 (130)
XQ201	Boost FET (IMS board)	115 (130)
Q1	Channel 1 output FET (adjacent to R4)	115 (130)
XU3	Primary driver IC	100 (130)
Various	All other electrolytic capacitors	80 (105)

### Additional Information

This report is an amendment of CBTR Ref. No. E135494-A33-CB-4, CB Test Certificate Ref. No. DK-44432-M1-UL dated 2015-03-27. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, it has been determined that the product continues to comply with the standard with only limited testing being required.

The following modifications were made:

1. Modification of the base PWB to accommodate an additional 2x discharge resistors with the relevant testing to show continued compliance.
2. Addition of alternate fan,
3. Updates to the CCL,
4. Updates to the enclosures.

### Technical Considerations

- Equipment was evaluated for a maximum supply tolerance of 90-264Vac and 120-350Vdc --
- The product was submitted and evaluated for use at the maximum ambient temperature (T<sub>ma</sub>) permitted by the manufacturer's specification of: 50°C (full load); 70°C (power and output current decreasing linearly by 2.5%/°C above 50°C) --
- The product is intended for use on the following power systems: IT (Norway only) TN, DC mains supply --
- The following were investigated as part of the protective earthing/bonding: Printed wiring board trace (refer to Enclosure - Schematics + PWB for layouts) --
- The following are available from the Applicant upon request: Installation (Safety) Instructions / Manual --
- The equipment disconnect device is considered to be: Provided by the end equipment --
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009+ +A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report). --
- Multi-layer PWB's accepted under CBTR Ref. No. E349607-A23 dated 2014-07-31 and letter report,



Enclosure 8-06 of this report. --

**Engineering Conditions of Acceptability**

When installed in an end-product, consideration must be given to the following:

- The end unit must be considered against clause 5.1.7 leakage current for input frequencies above 63Hz. --
- The following Production-Line tests are conducted for this product: Earthing Continuity Electric Strength --
- The following secondary output circuits are SELV: All --
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: Primary-SELV: 392 Vrms, 762 Vpk Primary-Earthed Dead Metal: 392 Vrms, 668 Vpk --
- The power supply terminals and/or connectors are: Suitable for factory wiring only --
- The investigated Pollution Degree is: 2 --
- Proper bonding to the end-product main protective earthing termination is: Required --
- The following end-product enclosures are required: Mechanical, Fire, Electrical --
- The following output terminals were referenced to earth during performance testing: All outputs and their return lines individually referenced to obtain maximum working voltage. --
- The maximum investigated branch circuit rating is: 16A (For IEC); 20A (For North America) --
- An investigation of the protective bonding terminals has: been conducted --
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJ3 insulation system with the indicated rating greater than Class A (105°C): Transformer TX2 (Class F) - See table 1.5.1 for details of insulation systems used. --
- The following secondary output circuits are at hazardous energy levels: Channel 1 output --
- The following components require special consideration during end-product Thermal (Heating) tests due to the indicated maximum temperature measurements during component-level testing: Input connector J1 (75°C) Common mode choke winding L1, L2 (130°C) X capacitors C7, C8 (100°C) Reservoir capacitor C9 (105°C) Boost choke winding L3 (140°C) Transformer winding TX2 (130°C) Transformer core TX2 (130°C) Transformer braid (to pin 13) TX2 (130°C) Optocoupler U2 (100°C) Channel 1 output capacitors C10, C11 (105°C) Primary choke (24V model only) L6 (130°C) Channel 1 Output choke L4 (130°C) Fan regulator XU2 or XU8 (130°C) Boost FET (IMS board) XQ201 (130°C) Channel 1 output FET (adjacent to R4) Q1 (130°C) Primary driver IC XU3 (130°C) All other electrolytic capacitors (105°C) --
- Fans: The fan provided in this sub-assembly is provided with a fan guard to reduce the risk of contact with the rotor. , The fan provided in this sub-assembly is not intended for operator access. --

Abbreviations used in the report:

- normal condition .....	N.C.	- single fault condition .....	S.F.C
- operational insulation .....	OP	- basic insulation .....	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation .....	SI
- double insulation .....	DI	- reinforced insulation .....	RI

Indicate used abbreviations (if any)