

	<p>Test Report issued under the responsibility of:</p>	
---	--	---

**TEST REPORT
IEC 60950-1
Information technology equipment - Safety -
Part 1: General requirements**

Report Reference No	4786910624-11
Date of issue	2015-09-15
Total number of pages	119

CB Testing Laboratory	UL Japan, Inc.
Address	4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan

Applicant's name	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER
Address	R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN

Test specification:	
Standard	IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013
Test procedure	CB Scheme
Non-standard test method	N/A

Test Report Form No.	IEC60950_1F
Test Report Form originator	SGS Fimko Ltd
Master TRF	Dated 2014-02

Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.


This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description	Switching Power Supply	
Trade Mark		
Manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN	
Model/Type reference	MTW30-51212xy, MTW30-51515xy x = "- or blank. y = 0-9, A-Z or blank	
Ratings	Input: AC 100–240V, 50–60Hz, 0.8–0.4A Output:	
	MTW30-51212xy	DC +5V/3.0A (4.5A peak), DC +12V/1.2A (2.0A peak), DC -12V/0.3A (0.45A peak) Total max. output power: 30W (peak load for 10s max., total power shall not exceed 30W during peak load)
	MTW30-51515xy	DC +5V/3.0A (4.5A peak), DC +15V/0.8A (2.0A peak), DC -15V/0.3A (0.45A peak) Total max. output power: 31.5W (peak load is for 10s max., total power shall not exceed 31.5W during peak load.)

Testing procedure and testing location:	
<input type="checkbox"/>	CB Testing Laboratory Testing location / address:
<input type="checkbox"/>	Associated CB Test Laboratory Testing location / address: Tested by (name + signature).....: _____ Approved by (name + signature)....: _____
<input checked="" type="checkbox"/>	Testing Procedure: TMP/CTF Stage 1 Testing location / address: TDK-LAMBDA CORPORATION, NAGAOKA TECHNICAL CENTER 2704-1 SETTAYA-MACHI, NAGAOKA-SHI, NIIGATA- KEN, 940-1195 JAPAN Tested by (name + signature).....: Ayano Matsumoto <i>A. Matsumoto</i> Approved by (name + signature)....: Tetsuo Iwasaki TetsuoIwasaki
<input type="checkbox"/>	Testing Procedure: WMT/CTF Stage 2 Testing location / address: Tested by (name + signature).....: _____ Witnessed by (name + signature) ..: _____ Approved by (name + signature)....: _____
<input type="checkbox"/>	Testing Procedure: SMT/CTF Stage 3 or 4 Testing location / address: Tested by (name + signature).....: _____ Approved by (name + signature)....: _____ Supervised by (name + signature) .: _____
<input type="checkbox"/>	Testing Procedure: RMT Testing location / address: Tested by (name + signature).....: _____ Approved by (name + signature)....: _____ Supervised by (name + signature) .: _____

List of Attachments

National Differences (24 pages)
Enclosures (28 pages)

Summary Of Testing

Unless otherwise indicated, all tests were conducted at TDK-LAMBDA CORPORATION, NAGAOKA TECHNICAL CENTER, 2704-1 SETTAYA-MACHI, NAGAOKA-SHI, NIIGATA-KEN, 940-1195 JAPAN.

Tests performed (name of test and test clause)	Testing location / Comments
Input: Single-Phase (1.6.2)	
Capacitance Discharge (2.1.1.7)	
SELV Reliability Test Including Hazardous Voltage Measurements (2.2.2, 2.2.3, 2.2.4)	
Limited Power Source Measurements (2.5)	
Protective Bonding II (2.6.3.4, 2.6.1)	
Humidity (2.9.1, 2.9.2, 5.2.2)	
Determination of Working Voltage; Working Voltage Measurement (2.10.2)	
Transformer and Wire /Insulation Electric Strength (2.10.5.13)	
Heating (4.5.1, 1.4.12, 1.4.13)	
Ball Pressure (4.5.5, 4.5)	
Touch Current (Single-Phase; TN/TT System) (5.1, Annex D)	
Electric Strength (5.2.2)	
Component Failure (5.3.1, 5.3.4, 5.3.7)	
Abnormal Operation (5.3.1 - 5.3.9)	
Transformer Abnormal Operation (5.3.3, 5.3.7b, Annex C.1)	
Power Supply Output Short-Circuit/Overload (5.3.7)	

Summary of Compliance with National Differences:

Countries outside the CB Scheme membership may also accept this report.

List of countries addressed: CA, DE, DK, EU, FI, GB, KR, SE, SI, US

The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013

Copy of Marking Plate - Refer to Enclosure titled Marking Plate for copy.

Test item particulars :

Equipment mobility	for building-in
Connection to the mains	not directly connected to the mains
Operating condition	continuous
Access location	N/A
Over voltage category (OVC)	OVC II
Mains supply tolerance (%) or absolute mains supply values	-10%, +6%
Tested for IT power systems	Yes
IT testing, phase-phase voltage (V)	230 V
Class of equipment	Not classified, class I construction
Considered current rating of protective device as part of the building installation (A)	Considered 20A (even though built-in application)
Pollution degree (PD)	PD 2
IP protection class	Not rated.
Altitude of operation (m)	≤ 2000 m
Altitude of test laboratory (m)	< 1000 m
Mass of equipment (kg)	Approx. 0.22kg

Possible test case verdicts:

- test case does not apply to the test object : N/A
- test object does meet the requirement : P(Pass)
- test object does not meet the requirement : F(Fail)

Testing:

Date(s) of receipt of test item	N/A
Date(s) of Performance of tests	2004-08 to 2004-09, 2006-01 2014-08-06 to 2014-08-28 2015-02-27

General remarks:

"(see Enclosure #)" refers to additional information appended to the report.
 "(see appended table)" refers to a table appended to the report.
 Throughout this report a point is used as the decimal separator.

Manufacturer's Declaration per Sub Clause 4.2.5 of IEC60950:

The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided Yes

When differences exist, they shall be identified in the General Product Information section.

Name and address of Factory(ies): TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI
81400 SENAI MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4
KAWASAN PERINDUSTRIAN
BANDAR BARU JAYA GADING
26070 KUANTAN MALAYSIA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI
TSUKUBA-SHI
IBARAKI-KEN 305-0831 JAPAN

GENERAL PRODUCT INFORMATION:**Report Summary**

All applicable tests according to the referenced standard(s) have been carried out.

Product Description

Built-in type switching power supply for use in general office equipment (host equipment is not specified).

Model Differences

Two models are identical to each other except for output ratings, transformer T1 and electrical ratings of secondary components.

Suffixes "x" and "y" are for marketing purpose only, not safety relevant.

Additional Information

This report is a reissue of CBTR Ref. No.:12027305 001, 12027305 002 and 12027305 003, CB Test Certificate Ref. No.JPTUV-048674, JPTUV-048674-M1, JPTUV-048674-M2. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, has been determined that the product continues to comply with the standard.

Sample Received date is 2014-09-16.

Construction review was conducted on 2014-09-19.

Abbreviations used in the report.

- built-in application: B/I

In this Test Report, CENELEC mark license indicating compliance to EN standard was used to verify component compliance to IEC standard because the standards are technically equivalent.

It was considered that UL Standard has requirements that meet or exceed the relevant IEC requirements.

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: 50°C

- The product is intended for use on the following power systems: TN
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The end-product Electric Strength Test is to be based upon a maximum working voltage of: max working voltage: 264 Vrms, 532 Vpk
- The following secondary output circuits are SELV: All output
- The power supply terminals and/or connectors are: Suitable for factory wiring only
- The maximum investigated branch circuit rating is: 20 A
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Not been conducted
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C): T1 (Class B)
- The following end-product enclosures are required: Fire, Electrical

Abbreviations used in the report:

- normal condition	N.C.	- single fault condition.....	S.F.C
- operational insulation	OP	- basic insulation	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation	SI
- double insulation	DI	- reinforced insulation	RI

Indicate used abbreviations (if any)